

19" Keystone Patch Panel 24 port angled with strain relief black

Description

This patch panel by Delock can be mounted in a **19" cabinet**. With its standardized dimensions, it is suitable for easy **snap-in mounting of 24 Keystone modules**.

Keystone modules for angled installation


The Keystone modules can be used angled to the right on one side and angled to the left on the other side. The **angled ports** ensure improved cable management and prevent bending damage when connecting patch cables.

Cable fixing for optimal cable management

On the back of the patch panel, the cables can be fixed with cable ties to enable clear and **orderly cable routing**.

Please Note

Due to the narrow design only keystone modules up to max. 17.8 mm width can be used.



Item no. 67042

EAN: 4043619670420

Country of origin: China

Package: Box

Technical details

- For mounting in 19" network cabinet, 1U
- 24 Keystone ports angled with 19.2 x 14.9 mm
- Material: metal / plastic
- Colour: black
- Dimensions (LxWxH): ca. 482.6 x 125.5 x 44.2 mm

Package content

- 19" patch panel
- Ground wire
- 12 x inscription label
- 25 x cable tie

Images



General

Mounting type:	19 in
----------------	-------

Physical characteristics

Material:	metal / plastic
Length:	482.6 mm
Width:	125.5 mm
Height:	44.2 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

