Fiber Optical Cable with metal armouring LC Duplex to LC Duplex Multi-mode OM3 1 m

Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.

With metal armouring
The robust fiber optical cables offer increased protection against damage and outer influences such as moisture, dust or damaging rodents. Despite the metal sheath, the cables remain bendable and flexible. The fiber optical cables are also characterised by their high tensile strength.



Item no. 87907

EAN: 4043619879076

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x LC Duplex >
  1 x LC Duplex
- Multi-mode OM3 cable with metal armour
- Fibre: 50/125 µm
- Ceramic ferrule with dust protection
- Cable diameter: ca. 3 mm
- Operating temperature: -20 °C ~ 70 °C
- LSZH (halogen-free)
- Colour: aqua
- Length incl. connectors: ca. 1 m

Package content

- Optical fiber cable

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Style:	both sides identical

Interface

Connector 1:	1 x LC Duplex
Connector 2:	1 x LC Duplex

Technical characteristics

Operating temperature:	-20 °C ~ 70 °C

Physical characteristics

Material:	LSZH (halogen-free)
Length:	1 m
Colour:	aqua
Cable diameter:	3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**