Adapter N plug to RP-SMA jack 10 GHz

Description

This adapter by Delock is suitable for connecting components of radio frequency technology.



Item no. 89984

EAN: 4043619899845

Country of origin: Taiwan, Republic of China

Package: Zip poly bag

Technical details

- Connectors:
  1 x N plug >
  1 x RP-SMA jack
- Housing: brass nickel plated
- Thread type: 1/4" - 36 UNS - 2A
- Frequency range: 10 GHz
- Impedance: 50 Ohm
- Operating temperature: -10 °C ~ 50 °C
- Dimensions (LxD): ca. 27.7 x 21.0 mm

System requirements

- Device with one free N or RP-SMA port

Package content

- Adapter

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Schnittstelle

Anschluss 1:	1 x N Stecker
Anschluss 2:	1 x RP-SMA Buchse

Technische Eigenschaften

Frequenzbereich:	10 GHz
Betriebstemperatur:	-10 °C ~ 50 °C

Physikalische Eigenschaften

Gehäusematerial:	Messing vernickelt
Durchmesser:	21,0 mm
Länge:	27,7 mm
Gewindetyp:	1/4" - 36 UNS - 2B

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**