Bellows suction cups (round)

FSGA 63 NK-45 G1/4-IG

Część nr..:10.01.06.00693


https://www.schmalz.com/10.01.06.00693

BalgChwytak podciśnieniowy (okrągła) z 1,5 Falten



- Size: 63
- Suction cup material: Natural Rubber NK
- Material hardness [Shore A]: 45 Shore A
- Nipple material: Aluminum
- Connection: G1/4"-F
- Number of folds: 1,5
- Vacuum connection: G1/4"-F

Dane projektowe



Atrybut	Wartość
d2	44,50 mm
Dmax(S)	68 mm
dn	4,40 mm
Ds	60 mm
G1	G1/4"-F
H	49 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	15 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	63
Number of folds	1,50
Connection	G1/4-IG
Curve radius (min) (convex)	100 mm
Volume	43,83 cm^3

Kontakt z firmą Schmalz
Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cups (round)

FSGA 63 NK-45 G1/4-IG

Część nr..:10.01.06.00693

https://www.schmalz.com/10.01.06.00693

Suction force (-600mbar)	85 N
Pull-off force	135 N
Hose diameter (empf.) d	6 mm
Weight	34 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N018 G1/4-IG DN440

Część nr..:10.01.06.01066

Nipple family: N 018
Thread G1: G1/4"-F
Length L1: 28,8 mm
Fitting length: 15 mm
Nominal diameter dn: 4,4 mm
Spanner size SW2: 5 mm
Material: Aluminum



FGA 63 NK-45 N018

Część nr..:10.01.06.00690

Size: 63
Suction cup material: Natural Rubber NK
Material hardness [Shore A]: 45 Shore A
Number of folds: 1,5