DIGITUS Professional CAT 5e U/UTP patch cord

DK-1512-020/BL
EAN 4016032318026



CAT 5e U-UTP patch cable, PVC AWG 26/7, length 2 m, color black

The DIGITUS® Category 5e Class D patch cords are manufactured and tested to the ISO/IEC 11801 and DIN EN 50173 Category 5e specifications. They will guarantee the installed cabling system is compliant with the ISO & EN channel specification requirements and will provide optimum performance levels of DIGITUS® Category 5e cabling. The performance is tested up to 100 MHz inclusive performance characteristics such as near end cross talk (“NEXT”). DIGITUS® patch cords are designed and produced to fulfill the highest requirements of various application areas in full volume. Each cable is fitted with a molded boot which comes with kink protection and strain relief. Furthermore the boot is equipped with a latch protection that prevents the latching lever against breaking.You can easily identify the Category 5e, because of the transparent blue colored connector.

Best performance and link quality for your network.

- 2x RJ45 (8P8C) connectors
- Boots with kink protection, strain relief and latch protection
- Length marking on boot
- Cable type: U/UTP
- Category: 5E
- Length: 2 m
- Type of connector connection 1: RJ45 8(8)
- Type of connector connection 2: RJ45 8(8)
- Colour outer sheath: Black
- Anti-kink sleeve: Moulded-on
- Locking lever: yes
- Colour anti-kink sleeve: Black
- Fire retardant version: no
- Halogen free: no
- Oil resistant (acc. EN 60811-404): no
- Cable construction: 4x2
- AWG-size: 26
- Pin assignment: 1:1
- NVP value: 69 %

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	150	7.50	36.00	36.00	24.00	31,104.00
Packaging Unit Inside	10	0.50	6.00	25.00	42.00	6,300.00
Packaging Unit Single	1	0.05	1.20	14.00	25.00	420.00
Net single without Packaging	1	0.04	200.00	1.17	1.27	297.18

Druckfehler, Irrtümer und technische Änderungen sind vorbehalten. | Printing errors, falsities and technical changes remain reserved.