


143
2-1/2" Swedish Model 90° Pipe Wrench 22"

PRODUCT DETAILS

- Single-component painted handle
- Slim design of the head allows excellent accessibility in confined spaces compared to many other types of pipe wrenches
- Gripping capacity up to 127 mm (5") and a jaw opening up to 160 mm (6 1/3)
- Patented progressive teeth for better grip
- Anti-rust treated high-alloy steel with induction hardened teeth
- The nut can be blocked in the desired position with the adjustment screw. Safety stop prevents threading-off
- Standards: DIN 5234



PRODUCT ATTRIBUTES

Product	A	B	C	D	max	g
143	557 mm	90 mm	19.8 mm	26.7 mm	2 1/2 in	2865 g