

HDMI UHD Splitter 1 x HDMI in > 4 x HDMI out 4K

Description

This splitter by Delock receives a HDMI signal from a PC or laptop and splits it to four connected displays. Thereby one HDMI connection can be used to operate four HDMI monitors.



Item no. 18684

EAN: 4043619186846

Country of origin: China

Package: Retail Box

Technical details

- Connector:
 - Input:
 - 1 x HDMI-A 19 pin female
 - 1 x DC 5 V power connector
 - Output:
 - 4 x HDMI-A 19 pin female
- High Speed HDMI specification
- Supports 3D displays
- Supports HDCP 1.4 and 2.2
- Supports HDR
- Reset button
- LED indicator
- Supports a resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Video bandwidth up to 600 MHz / 6 Gbps, 18 Gb/s max.
- Power consumption: max. 2.4 W
- Metal housing
- Colour: black
- Dimensions (LxWxH): ca. 123 x 51 x 20 mm

Power supply specification

- Power supply type: Euro wall power plug

- Model identifier: FJ-SW1160501000DE
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.3 A
- Output voltage / Output current / Output power: 5.0 V / 1.0 A / 5.0 W
- Average active efficiency: 75.7 %
- No-load power consumption: 0.07 W
- DC power connector: 5.5 x 2.1 mm
- Power supply cable length: ca. 1.5 m
- Ground outside, plus inside

System requirements

- A free HDMI female port
- HDMI cable

Package content

- HDMI Splitter
- USB power cable, length: ca. 0.5 m
- External power supply
- User manual

Images



General

Specification:	HDCP 1.4 HDCP 2.2 HDMI 2.0
----------------	----------------------------------

Interface

Output:	4 x HDMI-A female
Input:	1 x 5 V DC female 5,5 mm x 2,1 mm 1 x HDMI-A female

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
Video bandwidth:	600 MHz / 6 Gbps

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	123 mm
Width:	51 mm
Height:	20 mm

Power supply

Power supply type:	Euro wall power supply
Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.5 A
Power supply output:	5.0 V / 2.0 A
Power supply connector:	DC male 5.5 mm x 2.1 mm
Cable length of power supply:	1 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de