Qoltec Battery cable with connector terminals | Cable with eyelet | 20 cm | Black

Product code: 50988

A 10AWG battery cable with metal connector terminals is the ideal solution for installations requiring a solid and stable connection. High-quality copper conductors ensure maximum performance and minimal energy loss even under high current loads. Crimped connector terminals allow for immediate connection without soldering or additional tools.

BATTERY CABLE WITH RING TERMINALS, 10 AWG, 600 V

Durable and flexible insulation
The black flexible PVC coating guarantees resistance to abrasion, moisture and high temperatures, allowing the cable to retain its properties in harsh operating conditions. The flexible design makes it easy to route the cable in confined spaces, e.g. in battery boxes or device enclosures.

READY FOR INSTALLATION

High quality and reliable connection
The 10AWG (approx. 6 mm) battery cable with connectors has been designed for stable and safe power transmission. The pure copper core guarantees excellent conductivity and minimal voltage loss even under high current loads. The cable is terminated with metal connectors, enabling a quick, secure and durable connection – without the need for soldering or additional tools.

CONFIDENCE CONFIRMED BY A WARRANTY

The product is covered by a 24-month warranty period.
Do you care about the high quality of the product you buy? Our solutions will meet your expectations. The cables we offer are covered by a **24-month warranty** valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Type	Cable with eyelet
AWG cross section	10AWG
Insulation material	PVC
Usage	AGM, GEL, LiFePO batteries Converters, battery modules, solar inverters UPS emergency power supplies and PV systems Motorhomes, boats, electric vehicles
Additional information	Operating voltage up to 600V DC
OTHER PARAMETERS	
Colour	Czarny
Working temperature	-40 C do +105 C
Cable length	0.20m
Package contents	1 x Cable with eyelet
Package depth / length [mm]	200
Package height [mm]	10
Package width [mm]	10
Net weight [kg]	0.016
Gross weight [kg]	0.017
Warranty	24 month
EAN code	5901878509884