

BW 2047E/C108 Tool case with assortment of 108 general maintenance tools, in plastic case

14" 12"

555x370x92 mm

	Art.
020476308	BW 2047E/C108

- n. **BW 900:** Hexagon hand sockets, 1/4" □
 - n. **BW 900/25:** Universal joint - 1/4"
 - n. **BW 900/20:** Extension cords - 1/4"
 - n. **BW 900/20L:** Extension cords - 1/4"
 - n. **BW 900/30:** 1/4" drive spinner handle
 - n. **BW 900/42:** 1/4" drive sliding T-handle
 - n. **BW 900/55:** Reversible ratchet, 1/4" □
 - n. **BW 920A:** Hexagon hand sockets, 1/2" □
 - n. **BW 956C:** Spark plug sockets, 1/2" female square drive □
 - n. **BW 920/25:** Universal joint, 1/2"
 - n. **BW 920/21:** Extension bar - 1/2"
 - n. **BW 920/22:** Extension bar - 1/2"
 - n. **BW 910/16:** Adaptor - F3/8"xM1/2"
 - n. **BW 895/1:** Socket holders for items BW 861, BW 862, BW 866
 - n. **BW 42:** Combination wrenches □
 - n. **BW 96/SC9:** Set of 9 offset hexagon key wrenches □
 - n. **BW 1048:** Slip joint pliers, boxed joints
 - n. **BW 1080D:** Diagonal flush cutting nippers □
 - n. **BW 1150BM:** Heavy-duty combination pliers □
 - n. **BW 1166BM:** Extra-long needle knurled nose pliers □
 - n. **1201:**
 - n. **1202:**
 - n. **BW 1370:** Engineer's hammers
 - n. **BW 860EA/31:** Set of 30 bits with magnetic insert holder in pocket
- case B □ □ □ □
- n. **900E/55:**
 - n. **920E/55:**



14"					
	BW 900	□	4-5-5.5-6-6.5-8-9-10-11-12-13-14 mm		
	BW 900/25	□	125 mm		
	BW 900/20	□	50 mm		
	BW 900/20L	□	100 mm		
	BW 900/30	□	150 mm		
	BW 900/42	□	175 mm		

12"					
	BW 920A	□	10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-25-26-27 mm		
	BW 956C	□	16 mm-20mm-22mm-24mm-27mm-30mm		
	BW 920/25	□	257 mm		
	BW 920/21	□	125 mm		
	BW 920/22	□	200 mm		
	BW 910/16	□	1.34" 10"		

BW 860EA/31					
	1201	□	1202	□	1203
	1204	□	1205	□	1206
	1207	□	1208	□	1209
	1210	□	1211	□	1212
	1213	□	1214	□	1215
	1216	□	1217	□	1218
	1219	□	1220	□	1221
	1222	□	1223	□	1224
	1225	□	1226	□	1227
	1228	□	1229	□	1230
	1231	□	1232	□	1233
	1234	□	1235	□	1236
	1237	□	1238	□	1239
	1240	□	1241	□	1242
	1243	□	1244	□	1245
	1246	□	1247	□	1248
	1249	□	1250	□	1251
	1252	□	1253	□	1254
	1255	□	1256	□	1257
	1258	□	1259	□	1260
	1261	□	1262	□	1263
	1264	□	1265	□	1266
	1267	□	1268	□	1269
	1270	□	1271	□	1272
	1273	□	1274	□	1275
	1276	□	1277	□	1278
	1279	□	1280	□	1281
	1282	□	1283	□	1284
	1285	□	1286	□	1287
	1288	□	1289	□	1290
	1291	□	1292	□	1293
	1294	□	1295	□	1296
	1297	□	1298	□	1299
	1300	□	1301	□	1302
	1303	□	1304	□	1305
	1306	□	1307	□	1308
	1309	□	1310	□	1311
	1312	□	1313	□	1314
	1315	□	1316	□	1317
	1318	□	1319	□	1320
	1321	□	1322	□	1323
	1324	□	1325	□	1326
	1327	□	1328	□	1329
	1330	□	1331	□	1332
	1333	□	1334	□	1335
	1336	□	1337	□	1338
	1339	□	1340	□	1341
	1342	□	1343	□	1344
	1345	□	1346	□	1347
	1348	□	1349	□	1350
	1351	□	1352	□	1353
	1354	□	1355	□	1356
	1357	□	1358	□	1359
	1360	□	1361	□	1362
	1363	□	1364	□	1365
	1366	□	1367	□	1368
	1369	□	1370	□	1371
	1372	□	1373	□	1374
	1375	□	1376	□	1377
	1378	□	1379	□	1380
	1381	□	1382	□	1383
	1384	□	1385	□	1386
	1387	□	1388	□	1389
	1390	□	1391	□	1392
	1393	□	1394	□	1395
	1396	□	1397	□	1398
	1399	□	1400	□	1401
	1402	□	1403	□	1404
	1405	□	1406	□	1407
	1408	□	1409	□	1410
	1411	□	1412	□	1413
	1414	□	1415	□	1416
	1417	□	1418	□	1419
	1420	□	1421	□	1422
	1423	□	1424	□	1425
	1426	□	1427	□	1428
	1429	□	1430	□	1431
	1432	□	1433	□	1434
	1435	□	1436	□	1437
	1438	□	1439	□	1440
	1441	□	1442	□	1443
	1444	□	1445	□	1446
	1447	□	1448	□	1449
	1450	□	1451	□	1452
	1453	□	1454	□	1455
	1456	□	1457	□	1458
	1459	□	1460	□	1461
	1462	□	1463	□	1464
	1465	□	1466	□	1467
	1468	□	1469	□	1470
	1471	□	1472	□	1473
	1474	□	1475	□	1476
	1477	□	1478	□	1479
	1480	□	1481	□	1482
	1483	□	1484	□	1485
	1486	□	1487	□	1488
	1489	□	1490	□	1491
	1492	□	1493	□	1494
	1495	□	1496	□	1497
	1498	□	1499	□	1500

14"					
	BW 900	□	4-5-5.5-6-6.5-8-9-10-11-12-13-14 mm		
	BW 900/25	□	125 mm		
	BW 900/20	□	50 mm		
	BW 900/20L	□	100 mm		
	BW 900/30	□	150 mm		
	BW 900/42	□	175 mm		
	BW 920A	□	10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-25-26-27 mm		
	BW 956C	□	16 mm-20mm-22mm-24mm-27mm-30mm		
	BW 920/25	□	257 mm		
	BW 920/21	□	125 mm		
	BW 920/22	□	200 mm		
	BW 910/16	□	1.34" 10"		
	BW 895/1	□	1.34" 10"		
	BW 42	□	1201-1202-1203-1204-1205-1206-1207-1208-1209-1210-1211-1212-1213-1214-1215-1216-1217-1218-1219-1220-1221-1222-1223-1224-1225-1226-1227-1228-1229-1230-1231-1232-1233-1234-1235-1236-1237-1238-1239-1240-1241-1242-1243-1244-1245-1246-1247-1248-1249-1250-1251-1252-1253-1254-1255-1256-1257-1258-1259-1260-1261-1262-1263-1264-1265-1266-1267-1268-1269-1270-1271-1272-1273-1274-1275-1276-1277-1278-1279-1280-1281-1282-1283-1284-1285-1286-1287-1288-1289-1290-1291-1292-1293-1294-1295-1296-1297-1298-1299-1300-1301-1302-1303-1304-1305-1306-1307-1308-1309-1310-1311-1312-1313-1314-1315-1316-1317-1318-1319-1320-1321-1322-1323-1324-1325-1326-1327-1328-1329-1330-1331-1332-1333-1334-1335-1336-1337-1338-1339-1340-1341-1342-1343-1344-1345-1346-1347-1348-1349-1350-1351-1352-1353-1354-1355-1356-1357-1358-1359-1360-1361-1362-1363-1364-1365-1366-1367-1368-1369-1370-1371-1372-1373-1374-1375-1376-1377-1378-1379-1380-1381-1382-1383-1384-1385-1386-1387-1388-1389-1390-1391-1392-1393-1394-1395-1396-1397-1398-1399-1400-1401-1402-1403-1404-1405-1406-1407-1408-1409-1410-1411-1412-1413-1414-1415-1416-1417-1418-1419-1420-1421-1422-1423-1424-1425-1426-1427-1428-1429-1430-1431-1432-1433-1434-1435-1436-1437-1438-1439-1440-1441-1442-1443-1444-1445-1446-1447-1448-1449-1450-1451-1452-1453-1454-1455-1456-1457-1458-1459-1460-1461-1462-1463-1464-1465-1466-1467-1468-1469-1470-1471-1472-1473-1474-1475-1476-1477-1478-1479-1480-1481-1482-1483-1484-1485-1486-1487-1488-1489-1490-1491-1492-1493-1494-1495-1496-1497-1498-1499-1500		

Scan the QR Code to access the web tab
Specs, media and documentation in one click.

