



The advertisement features a silver VENTION 5-in-1 USB-C Hub with a black cable. The hub is shown in two orientations: standing upright and lying flat. The background is a vibrant blue with a subtle bokeh effect and a green monstera leaf on the right. The text 'USB-C 5-in-1 Hub' is prominently displayed in a large, bold, white font, with 'USB extension+charging' written below it in a smaller white font. At the bottom, four circular icons illustrate the hub's features: a 2x2 grid for '4 ports in Sync', a USB-C symbol for '100W PD fast charge', a smartphone and tablet for 'Phone/tablet connect to U disk /keyboard', and an SSD with a USB-C cable for 'Read mobile HDD'.

USB-C 5-in-1 Hub

USB extension+charging

**4 ports
in Sync**

**100W PD
fast charge**

**Phone/tablet
connect to U disk
/keyboard**

**Read
mobile HDD**

4 USB 3.0 Ports

Support 4 ports simultaneous in use



Mouse



Keyboard



Flash disk



Mobile HDD



Printer



Scanner



Cooler



USB desk fan



Graphic board



USB desk lamp



USB card reader

.....

Note: All data are from Vention Lab

PD 100W Fast Charging

Charging as well as operating the devices



Note: All data are from Vention Lab

4-Port USB3.0

5Gbps theoretical transmission speed

Note: All data are from Vention Lab



Connecting to Mouse and Keyboard

Flexible operation, no lag in gaming





Access to Mobile HDD

Drive 4TB mobile HDD and other devices
with external PD power supply

Note: All data are from Vention Lab

Laptop Connect to Printer

Support high power devices, office printing
and USB expansion in Sync




Mighty Internal Chip

VL815 chip for high-speed data transmission

HUB chip
VL817

PD chip
VL102



Note: The chip/circuit board is a rendering, please in kind prevail

Compatible for Various Systems

Support for Windows systems
Mac OS, etc., plug and play



Windows10



Windows8



Windows7



Vista



Windows XP



Mac OS



Android OS



iOS

Aluminum Alloy Texture

Anodizing treatment for premium heat dissipation



Anti-fingerprint



Aluminum
alloy material



Excellent
heat dissipation

Portable Size

Easy for carrying around



Explore More Potential

No need for network

Movies/documents
read in any time



Transformed to a computer

Convenient
for mobile office



Phone connect to gamepad

Become
a game master



Note: The phone/tablet must support OTG function

Product Parameters

Brand: Vention

Name: USB-C to USB3.0x4/PD Hub Aluminum Alloy Type

Model: TNBHB

Color: Gray

Interface: USB-C/USB 3.0x4/PD

Interface Technics: Nickel-plated

Transmission Speed: 5Gbps

Rated Input: PD 100W

Conductor: Tinned-copper

Shell: Aluminum Alloy

Chip: VL817(Hub)/VL102(PD)

Shielding: Aluminum Foil + Metal Braided

Jacket: TPE

AWG: 32AWG+24AWG

OD: 4.5mm

Length: 0.15m

Warranty: 1 Year

Packing: Kraft Box+Color Box



Note: All data are from Vention Lab.

Sizes above are manually measured. There might be slight tolerance.



Note: Packing difference exists for different meters or batches.
The photo is for reference only



5-in-1 USB-C Hub

Technical Features	
Color	Gray
Interface	USB-C/USB 3.0 x 4/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Data transfer rates	5Gbps (USB 3.0)
Power supply	100W PD

Length	Art.No.	EAN Code
0.15m	TNBHB	6922794753518



Package Contents
5-in-1 USB-C Hub x 1

Packaging Information	
Packing Dimension	17.25*9.25*2.75cm
Packing Weight	0.11kg
Carton Dimension	48*29*30cm
Carton Qty	70pcs
Carton Weight	8.7kg