SCART cable

RoHS Conformity



Applications:
Special cable composed of: 2 + 4 separately shielded and insulated cores, 4 shielded cores and 3 insulated cores.
Suitable to connect SCART 21 poles plug:

2	Video IN	(Pin 20-17)
	Video OUT	(Pin 19-17)
+4	Video R.G.B.	(Pin 15/13 - 11/9 - 7/5)
	Switch	(18/16)
+4	Audio stereo IN	(Pin 6-2-4)
	Audio stereo OUT	(Pin 3-1-4)
+3	Data 1-2	(Pin 12-10 / 14*17)
	Power +8V.	(Pin 8)

Characteristics:

Conductors:	O.F.C. red copper
Cond. Insulation:	PVC
Core colours:	2 Transparent
	+4 Yellow
	+4 Black, Red, Yellow, White
	+3 Grey, Red, Blue
Shields:	2+4 Spiral covering **100%**
	4 Braided covering **90%**
	O.F.C. red copper
Inner Sheaths:	PVC
Inner Sheath colours:	2 Black, Grey
	+4 Red, Green, Blue, White
	+4 White
External Sheath:	PVC
Sheath colour:	Black



tasker® Code	Cond. number	Nominal section mm²	Cond. Format. mm.	External Core Ø mm.	External Inner Sheath Ø mm.	External Cable Diameter mm.	Reel or Spool (* pag. II) mt.	Type	Kg.
C183	2	2 x 0,25 (23 AWG)	32x0,10	1,9	2,3	11,0	100	B	18,0
	+4	+4 x 0,25 (23 AWG)	32x0,10	1,2	4,4				
	+4	+4 x 0,25 (23 AWG)	32x0,10	1,2					
	+3	+3 x 0,25 (23 AWG)	32x0,10	1,5					

Conductor Resistance Ω/Km ± 5%	Capacity Core/core pF/mt	Capacity Core/shield pF/mt
75		130
75		360
75		240
75		

Max rated Voltage AC - V	Operative Temperature °C
49	-15 / +70

Notes: