LTE Antenna N jack 4 - 6 dBi 22 cm omnidirectional fixed wall and pole mounting white outdoor

Description

This antenna by Delock allows the usage of different LTE bands outdoors.



Item no. 12571

EAN: 4043619125715

Country of origin: China

Package: Box

Technical details

- Connector: 1 x N jack
- Frequency range: 698 - 2700 MHz
- ZigBee, LoRa, DECT, Z-Wave, NB-IoT, Bluetooth, GSM, UMTS, LTE, ISM, WLAN
- Antenna gain: 4 - 6 dBi
- Impedance: 50 Ohm
- VSWR
- Polarisation: vertical
- Horizontal beamwidth: 360°
- VBW vertical beamwidth: 25°
- Operating temperature: -50 °C ~ 80 °C
- Housing material: GFRP
- Colour: white
- Dimensions (LxD): ca. 220 x 69 mm
- Weight: ca. 0.5 kg

System requirements

- Device with one free N port

Package content

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Antenna
- Mounting material: nut, washer, mounting bracket and pole mounting bracket

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Suitable for outdoor:	yes

Interface

Connector:	1 x N female

Technical characteristics

Frequency range:	698 - 2700 MHz
Antenna gain:	4 - 6 dBi
Beam width horizontal:	360°
Beam width vertical:	25°
Impedance:	50 Ω
Operating temperature:	-50 °C ~ 80 °C
Polarisation:	vertical
VSWR:	1.5

Physical characteristics

Weight:	0.5 kg
Dimensions (LxD):	22.0 x 6.9 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**