USB Type-C™ Network Adapter Gigabit LAN 1 x RJ45 PoE with USB Power Delivery

Description

This USB network adapter by Delock offers a reliable and fast network connection. With a transmission speed of up to 1 gigabits per second, it enables efficient working and smooth streaming.

Integrated LAN PoE+ PD connection with USB Power Delivery

The adapter is a PoE-powered device and can draw power directly from the network cable. It also has a built-in USB charging function, that enables it to charge a connected smartphone or tablet via USB Type-C™ Power Delivery. This means that only a single cable is required for both the network connection and the power supply.



Item no. 81633

EAN: 4043619816330

Country of origin: China

Package: Box

Technical details

- Connectors:
  1 x USB 5 Gbps USB Type-C™ male
  1 x Gigabit LAN RJ45 jack
- Chipset: Realtek RTL8153
- Output power PD for host: max. 15 W
- Data transfer rate:
  Ethernet up to 10 Mbps
  Fast Ethernet up to 100 Mbps
  Gigabit Ethernet up to 1000 Mbps
- Compatible with:
  IEEE 802.3: 10BASE-T
  IEEE 802.3u: 100BASE-TX
  IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Supports IEEE 802.3x full duplex flow control
- Supports 9k Jumbo Frames
- Supports IEEE 802.3af PoE
- Supports IEEE 802.3at PoE+
- LED indicator for link and activity
- Robust aluminum housing
- Colour: anthracite
- Cable length without connectors: ca. 60 cm

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Dimensions (LxWxH): ca. 96 x 49 x 25 mm

System requirements

- Android 14.0 or above
- Linux Kernel 6.5 or above
- Mac OS 14.5 or above
- Windows 11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3/4/5 port

Package content

- USB Type-C™ Gigabit LAN adapter
- User manual

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Allgemein

Unterstütztes Betriebssystem:	iPad Pro (3. Generation) oder höher iPad Air (4. Generation) oder höher Windows 11 Android 14.0 oder höher Linux Kernel 6.5 oder höher Mac OS 14.5 oder höher
LED Anzeige:	Verbindung und Aktivität

Schnittstelle

Anschluss 1:	1 x USB 5 Gbps USB Type-C™ Stecker
Anschluss 2:	1 x Gigabit LAN RJ45 Buchse

Technische Eigenschaften

Chipsatz:	Realtek RTL8153
Datentransferrate:	Ethernet bis zu 10 Mbps Fast Ethernet bis zu 100 Mbps Gigabit Ethernet bis zu 1 Gbps

Physikalische Eigenschaften

Gehäusematerial:	Aluminium
Kabellänge:	60 cm
Länge:	96 mm
Breite:	49 mm
Höhe:	25 mm
Farbe:	anthrazit

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**