Rating	16A 125V AC 1/8HP 10A 250V AC 1/3HP	Mounting Hole	Circuit Diagram
	10A 250V~		
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P DPST ON-OFF(Illuminated)		



Thickness	X	Y
0.75...1.25	30.2-0.1	22.2+0.1
1.25...2	30.4-0.1	22.2+0.1
2...3	30.8-0.1	22.2+0.1



Material:
Frame: Nylon# 66
Actuator: PC
Printed: None

原稿

RD 原稿 71005-1/24



1820500	Black	Green
1820471	Black	Red /120V
1820485	Black	Red /110V
SCI NO.	Frame	Actuator

C8\R13\R13-69B-01(1820485,471,500)

Date	Name	Description	NO
			△
			△

Drawn	Checked	Approved	SCI BOM NO.	SEE TABLE	Model Name	ROCKER SWITCH	
曹盈芳	[illegible]	[illegible]	Customer No.		Model No.	R13-69B-01	REV.
09/12/'07	P/13/07	9/13/07	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		0