

3 Port USB 3.2 Gen 1 Hub + Gigabit LAN with USB Type-C™ or USB Type-A connector

Description

This solid USB hub by Delock with metal housing can be connected to a computer, laptop or mobile device via the USB Type-A or USB-C™ interface. Up to 3 USB devices can be connected to the hub.

Integrated 10/100/1000 Mbps LAN interface

In addition, the hub with integrated RJ45 Gigabit LAN connection expands a PC or laptop by a network interface.

Extensive connectivity

Due to the specially designed adapter, the Delock hub can be quickly and easily connected to the USB Type-A socket. Thus, it can be easily connected to new devices with USB Type-C™ female and older devices that only have a USB Type-A connector. The adapter is located directly on the cable and therefore it cannot be lost.

Small sturdy helper

Due to its small dimensions and its sturdy housing, this Delock Hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 64149

EAN: 4043619641499

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ male >
 - 3 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
 - 1 x Gigabit LAN RJ45 jack
- Adapter:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female >
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A male
- Chipset: Genesys Logic GL3510, ASIX AX88179
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:

IEEE 802.3: 10BASE-T
IEEE 802.3u: 100BASE-TX
IEEE 802.3ab: 1000BASE-T

- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports Wake On LAN (WOL)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure
- Supports 4k Jumbo Frames
- Robust metal housing
- Dimensions (LxWxH): ca. 90 x 23 x 13 mm
- Cable length incl. connector: ca. 20 cm
- Colour: black
- Plug & Play

System requirements

- Chrome OS
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Linux Kernel 5.8 or above
- Mac OS 11.1 or above
- Windows 8.1/8.1-64/10/10-64
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port or
- A free USB Type-A port

Package content

- USB hub + LAN
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 5.8.0 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Mac OS 11.1 or above

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	3 x USB 5 Gbps Type-A female
Connector 3:	1 x Gigabit LAN RJ45 jack

Technical characteristics

Chipset:	Genesys Logic GL3510 ASIX AX88179
Data transfer rate:	5 Gbps

Physical characteristics

Cable length:	20 cm
Length:	90 mm
Width:	23 mm
Height:	13 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de