




USB Cable

USB-C To C+USB Cable

Fast charging, perfect conversion



3A high
current

480Mbps
transmission

Support fast
charging

Applicable to
USB-C devices

PD charging

About 1.5 hours Full of MacBook Air 13"

Support 20V/3A, PD60W fast charge, can quickly charge laptops




Note: All data are from Vention Lab

PD charging

About 2.5 hours Full of iPad Pro 11"

Support PD18W, safe and time-saving charging



Note: All data are from Vention Lab

PD charging

About 2.5 hours Full of Nintendo Switch

Perfect game companion



Note: All data are from Vention Lab

FCP/QC fast charging

3A Current Fully Charge in Less Time

Support Huawei FCP/Qualcomm QC 4.0 and
other fast charge technologies

80 minutes

Full of Huawei Nova5i Pro
4000mAh



59 minutes

Full of Galaxy S20 Ultra
5000mAh



Note: All data are from Vention Lab, should be used with compatible fast chargers

Fast Data Transmission

Standard USB 2.0 interface, 480Mbps transmission speed



USB-C phone

Connect to USB PC



USB-C phone

Connect to USB-C PC


Note: All data are from Vention Lab

Applicable USB-C Devices

	Laptop	Cellphone
Apple	MacBook12", MacBook Pro 2019 Mac Mini, MacBook Air 2020	Huawei Nova5/6/7 Mate20/30, Mate20/30 Pro Mate20/30 RS P20/30/40 P20/30/40 Pro
Huawei	MateBook, MateBook X/E MateBook 13/14	
Honor	MagicBook, MagicBook 2019	
Xiaomi	Air12.5"/13.3", GTX version 15.6" Xiaomi game book 8 generation	
HP	Pavilion x2, Spectre 13 EliteBook Folio G1, Envy 13 Shadow Wizard 4 Pro	Honor 30, 30S, V30 V20, Magic2 Note 10, V10
ASUS	Ling Yao 3, Ling Yao 3 Pro Ling Yao X series, U306, U321 U4100UN, U5100UQ, ROG	Microsoft Microsoft 950XL Microsoft 950
Dell	XPS13/15, Latitude 5285, G+C22 G3/G5/G7, Lingyue 5000/7000	Xiaomi 9/10 Pro, 9/10 8/9se, 8, 8 Lite Redmi Note7 Redmi K20/K30
Lenovo	Xiaoxin Air 12", Yoga5/6 Pro ThinkPad_X1 Carbon 2017 Saver Y7000/Y7000P/Y9000K	
SAMSUNG	NoteBook series GalaxyBook series	LG G5, V300L
Google	ChromeBook Pixels PixelBook Pen	Samsung S10, S10+, S10e A9s, A9 Stat Note8/9/10
Razer	Blade Stealth Spirit Blade Spirit Blade Sneak Edition	
Microsoft	Surface Book 2, Surface GO	Meizu 16/17th, X8
HTC	HTC 10	vivo Z5, iQOO, X27
Tablet	Apple iPad Pro 2018/2020	OPPO R17 Pro
	Huawei MediaPad M5	Smartisan Nut Pro 2S
	Xiaomi MI PAD 4	BlackShark BlackShark 2
Game Machine	Nintendo Switch	
More USB-C models will be continuously updated ...		

Safeguard Your Battery

Thickened tinned-copper conductor with multiple shielding technologies for battery protection



Smooth Plug in/out

One-piece moulding design, enhanced swapping times

3000+

USB interface
swapping test

10000+

USB-C interface
swapping test




Note: All data are from Vention Lab

Delicate Details

**Nickel-plated
interface**
Anti-rust and antioxidant

TPE jacket
Wear resistance

Extra long tail
Bending resistance



Product Parameters

Brand:Vention	Shell:PVC
Name:USB 2.0 C&USB-A Male to USB-C Male Cable	
Model:CQLB	Jacket:TPE
Color:Black	AWG:21+27AWG
Interface:USB 2.0 C Male/USB 2.0 A Male	OD:4.0mm
Interface Technics:Nickel-plated	Length:0.5/1m
Transmission Rate:480Mbps	Rated Current:3A(Max)
Conductor:Tinned-copper	Warranty:1 Year
Shielding: Aluminum Foil+Metal Braided+GND	Packing:PE Bag



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance



Note: Packing difference exists for different meters or batches.
The photo is for reference only

Length	Art.No.	EAN Code
0.5m	CQLBD	6922794752979
1m	CQLBF	6922794752986



Package Contents

USB Cable x 1

Packaging Information

Packing Dimension	cm	
Packing Weight	kg	
Carton Dimension	48*29*30cm (0.5-1m)	
Carton Qty	300pcs(0.5m),200pcs(1m)	www.ventioncable.com
Carton Weight	9.1kg(0.5m)	
Package	PE bag	