

DisplayPort 1.2 Splitter 1 x mini DisplayPort in > 2 x DisplayPort out 4K

Description

This splitter by Delock receives a DisplayPort signal from a PC or laptop and splits it to two connected displays. Thereby one mini DisplayPort connection can be used to operate two DisplayPort monitors. Both outputs are dual-mode capable (DP++), so that HDMI or DVI monitors can be connected with suitable adapters.



30 cm

Please Note

The product is a Multi-Stream Transport (MST) hub and supports the extended desktop configuration of DisplayPort 1.2. When Mac OS is used, the same image is displayed on both ports (mirrored), it is not possible to use both ports independently of each other.

Item no. 87695

EAN: 4043619876952

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connectors:
Input: 1 x mini DisplayPort 20 pin male
Output: 2 x DisplayPort 20 pin female
- Chipset: STDP4320
- DisplayPort 1.2a specification
- Active converter, Single- / Multi-Stream Transport Hub (SST / MST)
- Functions: Mirrored or Extended (Windows only)
- Maximum resolution (depending on the system and the connected hardware):
DisplayPort 1.1 or 1.2 Single-Stream Transport (SST):
up to 1920 x 1080 @ 60 Hz (mirror)
DisplayPort 1.2 Multi-Stream Transport (MST):
up to 2560 x 1440 @ 60 Hz or 3840 x 2160 @ 30 Hz (mirror or extended)
- DisplayPort output supports Dual Mode DP++
- Supports Eyefinity / Single Large Surface (SLS)
- Audio input formats: 7.1 channel up to 192 kHz sample rate
- Metal housing
- Colour: black
- Cable length without connectors: ca. 30 cm
- Dimensions (LxWxH): ca. 100 x 67 x 23 mm


System requirements

- Mac OS 10.12 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- A free mini DisplayPort female

Package content

- DisplayPort Splitter
- User manual

Images



General

Specification:	DisplayPort 1.2a
----------------	------------------

Interface

Output:	2 x DisplayPort female
Input:	1 x mini DisplayPort 20 pin male

Technical characteristics

Chipset:	Kinetic STDP4320
Maximum screen resolution:	3840 x 2160 @ 30 Hz

Physical characteristics

Housing material:	metal
Cable length incl. connectors:	30 cm
Length:	100 mm
Width:	67 mm
Height:	23 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de