




Technical manual
Instrukcja techniczna
Technische Anleitung
Manuel technique



Y¹ → 208

mounting plate Y
uchwyt Y
Halter Y
fixation Y

Y² → 208

mounting plate Y cone
uchwyt Y cone
Halter Y cone
fixation Y cône

T¹ → 204

mounting plate T
uchwyt T
Halter T
fixation T

T² → 204

connector T 180 deg
łącznik T 180 st
Verbinder T 180 Grad
connecteur T 180 degrés

E → 198

diffuser E slide
klosz E wsuwany
Abdeckung E einschiebbar
diffuseur E coulissant

F → 199

diffuser F click
klosz F klik
Abdeckung F einclipsbar
diffuseur F clic

E7 → 198

diffuser E7 click
klosz E7 klik
Abdeckung E7 einclipsbar
diffuseur E7 clic

1* → 198

end cap E7
zaślepka E7
Endkappe E7
embout E7




white painted
biały malowany
weiß lackiert
peint en blanc



anodized
anodowany
eloxiert
surface anodisée



black anodized
czarny anodowany
schwarz eloxiert
noir anodisé



raw aluminium
surowe aluminium
Rohaluminium
aluminium brut

1000 mm
2000 mm
3000 mm
4050 mm


A3010001
A3020001
A3090001
A3120001

A3010020
A3020020
A3090020
A3120020

A3010021
A3020021
A3090021
A3120021

A3010000
A3020000
A3090000
A3120000

end cap GROOVE14 gen2 with hole
zaślepka GROOVE14 gen2 z otworem
Endkappe GROOVE14 gen2 mit Öffnung
embout GROOVE14 gen2 avec un trou



white
biały
weiß
blanc

A3970001

silver
srebrny
silbern
argent

A3970040


black
czarny
schwarz
noir

A3970002

grey
szary
grau
gris

A3970022

end cap GROOVE14 gen2 SQ with hole
zaślepka GROOVE14 gen2 SQ z otworem
Endkappe GROOVE14 gen2 SQ mit Öffnung
embout GROOVE14 gen2 SQ avec un trou



white
biały
weiß
blanc

A3980001

silver
srebrny
silbern
argent

A3980040

black
czarny
schwarz
noir

A3980002

grey
szary
grau
gris

A3980022

connector GROOVE14 90 deg
łącznik GROOVE14 90 st
Verbinder GROOVE14 90 Grad
connecteur GROOVE14 90 degrés

material: aluminium
materiał: aluminium
Material: Aluminium
matériel: aluminium



white painted
biały malowany
weiß lackiert
peint en blanc

A3990001

anodized
anodowany
eloxiert
surface anodisée

A3990020

black anodized
czarny anodowany
schwarz eloxiert
noir anodisé

A3990021