

Active USB Type-C™ to HDMI Adapter (DP Alt Mode) 4K 60 Hz (HDR)

Description

This Delock adapter is suitable for the connection of an HDMI monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



Item no. 66571

EAN: 4043619665716

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male >
 - 1 x HDMI-A female
- Chipset: Parade PS186
- DisplayPort 1.4 and High Speed HDMI specification
- Signal direction: USB Type-C™ input > HDMI output
- Cable gauge:
 - 32 AWG data line
 - 28 AWG power line
- Cable diameter: ca. 5 mm
- Connectors: gold-plated
- Metal housing
- Transmission of audio and video signals
- Data transfer rate up to 18 Gbps
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Supports HDR
- Supports HDCP 1.4 and 2.3
- USB bus powered
- 1 x ferrite core
- Cable length without connectors: ca. 20 cm
- Colour: grey / black

System requirements

- Android 6.0 or above
- iPad Pro (2018)
- Linux Kernel 4.6.4 or above
- Mac OS 10.15 or above
- Windows 8.1/8.1-64/10/10-64
- Windows 10 Mobile
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI adapter

Images



General

Specification:	DisplayPort 1.4 HDCP 1.4 HDCP 2.3 HDMI 2.0 HDR
Supported operating system:	Mac OS 10.15.1 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI-A female

Technical characteristics

Chipset:	Parade PS186
Data transfer rate:	18 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Ferrite core:	1 x
Cable length:	20 cm
Pin finishing:	gold-plated
Cable gauge:	32 AWG data line 24 AWG power line
Material:	Aluminium PVC
Length:	45 mm
Height:	10 mm

Colour:	grey black
Cable diameter:	5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de