

# HDMI Switch 5 x HDMI in to 1 x HDMI out 8K 60 Hz

## Description

With this HDMI switch by Delock up to **five HDMI devices** can be used with one HDMI monitor, TV or projector. The button on the device or the remote control can be used to switch between the HDMI devices.

## USB powered

The device is powered via a USB port, a suitable USB cable is included. If no free USB-A port is available, an optional external power supply is required.



**Item no. 18657**

EAN: 4043619186570

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:  
Input:  
5 x HDMI-A female  
1 x USB Type-C™ female (5 V power supply)  
Output:  
1 x HDMI-A female
- HDMI port switching: automatic function, via button or via infrared remote control
- LED indicators for active HDMI port
- Ultra High Speed HDMI specification
- Supports HDCP 1.4 and 2.3
- Supports HDR
- Supports CEC
- Supports Game Mode VRR
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Resolution up to:  
7680 x 4320 @ 60 Hz  
3840 x 2160 @ 144 Hz  
(depending on the system and the connected hardware)
- Video bandwidth up to 1200 MHz / 12 Gbps, max. 48 Gbps
- Power consumption: max. 5 W
- Robust metal housing
- Colour: black
- Dimensions (LxWxH): ca. 161 x 61 x 14 mm

---

## System requirements

- HDMI cable
- Power source with a free USB Type-A female port
- 2 x AAA battery

---

## Package content

- HDMI switch
- Remote control
- USB power cable, length: ca. 1 m
- User manual

---

## Images



## General

|                |                                         |
|----------------|-----------------------------------------|
| Specification: | HDCP 1.4<br>HDCP 2.3<br>HDMI 2.1<br>HDR |
|----------------|-----------------------------------------|

## Interface

|         |                                                            |
|---------|------------------------------------------------------------|
| Output: | 1 x HDMI-A female                                          |
| Input:  | 5 x HDMI-A female<br>1 x USB Type-C™ female (power supply) |

## Technical characteristics

|                            |                                             |
|----------------------------|---------------------------------------------|
| Maximum screen resolution: | 7680 x 4320 @ 60 Hz<br>3840 x 2160 @ 144 Hz |
|----------------------------|---------------------------------------------|

## Physical characteristics

|                   |        |
|-------------------|--------|
| Housing colour:   | black  |
| Housing material: | metal  |
| Length:           | 160 mm |
| Width:            | 61 mm  |
| Height:           | 14 mm  |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |