



Qoltec Uninterruptible Power Supply | Monolith | 450VA | 240W | LCD | USB | RJ45

Product code: 53977

Qoltec off-line UPS is a modern and economical device that ensures stable operation of the computer even in the event of a power cut.

It's perfect for anyone who wants to have control over the stable operation of their devices regardless of fluctuations in the power supply.

Discover secure energy

Each of us has had to deal with low tensions at home or at work many times. Sometimes they only have the effect of needing to restart the computer. But how many times as a result of such an event have you lost important unsaved data or encountered a device failure? **If the above situations are familiar to you, we have a solution for you**, thanks to which the **problems of voltage decay or voltage drops will not apply to you**. Qoltec UPS uninterruptible power supply is a solution that provides a constant supply of energy necessary for the stable operation of your computer.

Get to know a better format of work

Our solution also offers:

- **automatic voltage regulation (AVR)** - not only stable power supply and lower battery consumption, but most of all protection of the device against too high / low voltage,
- **cold start** - a very useful function - in the event of a power failure, you can turn on, for example, a computer by connecting to the UPS, itself. This allows you to quickly, for example, copy important files to a USB stick or send an important e-mail at any time.
- overload, discharge and overcharge **protection**,
- **USB port** - thanks to the power supply management software, you monitor its operation on an ongoing basis and adapt it to your needs,
- **audible alarm** to indicate **low battery level** and **audible fault indication**.

Ease of use for your comfort

The built-in **LCD display** guarantees you easy management of the device operation. You receive information about the status and parameters on an ongoing basis, which makes **working with the power supply easy, fast and reliable**.

You don't have to stop your activity

The UPS is equipped with a **maintenance-free battery** guaranteeing you **stable operation during an emergency power supply to your computer**. During this time you will **save important data to disk or finish the next level of your game**. The battery charging process to 90% efficiency takes up to 6 hours.

Trust confirmed by warranty

Do you care about the high quality of the product you buy? **Our solutions will meet your expectations**. Each of the UPS Line Interactive uninterruptible power supplies we offer is covered by a 24-month warranty valid from the date of purchase.

Technical data

Producer	Qoltec
Rated capacity	450 VA
Usable power	240 W
Wave form	Simulated sine wave
Transfer time	2 – 6 ms
Range voltage	Input voltage range: 140 Vac ~ 300 Vac Output voltage: 220 V ± 10% Input frequency: 50/60 Hz ± 1 Hz
Usage	Data processing centers Industrial and production environments Medical centers Application in places where operational reliability is required
Built-in battery	1 x 12V / 4.5Ah
Battery quantity	1
Battery voltage	12 V
Output sockets	2 x SCHUKO (type F CEE 7/3) 1 x USB type B (port for communication with the device)) 2 x RJ45
Charging time	4-6 hours to 90% capacity
Noise	Less than 40dB
Safety	- Overload protection - Against discharge - Against overcharging
Functions	Cold start Audible alarm to indicate low battery level Audible signaling of a fault
Screen	LCD
Additional information	Uninterruptible power supplies (UPS) for telecommunications equipment and for automatic data processing equipment. It provides a "reserve" of energy in the event of a power failure, thus protecting against data loss.
Package contents	UPS with built-in power cord (1 x SCHUKO type E) 1.15 m USB cable Software CD User manual Warranty card
Housing color	Black
Dimensions	286 x 100 x 144 mm
Package depth / length	323 mm
Package width	142 mm
Package height	222 mm
Net weight	3,5440 kg
Gross weight	3,8950 kg
Warranty	24 months
EAN code	5901878539775