

MINI SLIM

Ultra-thin rechargeable work light




MINI SLIM is a small USB-C rechargeable LED work light that offers the perfect combination of convenience and versatility. It is a 3-in-1 solution that serves as an inspection light, work light, and flashlight - all in one compact and portable handlamp.

With the ultra-thin design of the light strip (only 9 mm), it is perfect for reaching the most narrow and inaccessible work areas. This makes MINI SLIM ideal for very demanding and difficult inspection jobs. It has a built-in magnet and hook, as well as a flexible 100 % foldable body that offers flexible positioning options. The design allows for traditional hand-held use, and its compact size ensures portability anywhere. When folded, it easily transforms into a flashlight that provides a firm grip. In addition, a user-friendly battery indicator keeps you informed about the battery level.



Powered by a high efficiency multi-LED design of 16 LEDs, MINI SLIM offers an adjustable light output up to 200 lumen. The top light provides a focused beam of 100 lumen. The OPTILight setting delivers the required illuminance (LUX) in a typical work situation, ensuring optimized light and runtime with a simple touch. This work light provides a constant lumen output performance measured according to the European standard EN 13032-1.



MINI SLIM	
Product number	03.6210
Light source	High efficiency multi-LED design with 16 LEDs
Luminous flux, lumen	20-200 Spot: 100
OPTILight setting	500 lux@0.25 m
Adjustable light output	3 levels
Beam angle	110° Spot: 25°
CRI	Ra > 80
CCT	5700 K
Operating time max. / min. lumen, h	2/19
Operating time OPTILight, h	5.5
Charging time, h	2.5
Battery	3.7 V/800 mAh Li-ion
Verified no. of charging cycles	Min. 1000
Protection class	IP30
Rough service	-
Impact protection	IK07
Impact resistance	2 m
Cable	1 m USB-A to USB-C
Operating voltage AC	-
Charging voltage/current DC	5 V / 1 A
Power consumption	1.4 W
Charger incl.	No
Operating temperature	-10 to +40 °C
Dimensions	130 x 43 x 29 mm
Net weight	97 g



03.6210 MINI SLIM

03.5610 MINI SLIM
Previous version

PRODUCT IMPROVEMENTS

- 30 % efficiency improvement
- 18 % recycled material
- OPTILight functionality
- Dedicated buttons for on/off and brightness levels
- Battery indicator
- Double temperature surveillance to protect the lamp and battery
- Min. 1000 charging cycles
- Warranty extended from 3 to 5 years
- New colour scheme

A pioneering approach that focuses on reinventing the design and functionality of LED work lights and optimizing energy efficiency to the utmost. With a focus on sustainability, traditional standards are rethought, and boundaries are pushed to extend the lifespan of lighting solutions.



5
years
warranty

Read terms and register on
scangrip.com to activate
your warranty