

USB Type-C™ Adapter to Combo HDMI / DisplayPort 8K

Description

This adapter by Delock is suitable for the connection of an **HDMI or DisplayPort** monitor in **8K Ultra HD** resolution to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 or Thunderbolt™ 4 interface.



Dualport - HDMI / DisplayPort combo female

The specially designed **Dualport port** allows the connection either an HDMI plug or a DisplayPort plug.

Item no. 64316

EAN: 4043619643165

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x HDMI / DisplayPort combo female
- Chipset: VIA VL605
- DisplayPort 1.4 specification
- Maximum resolution (depending on the system and the connected hardware):
 - DisplayPort up to 7680 x 4320 @ 120 Hz
 - HDMI up to 7680 x 4320 @ 60 Hz
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- USB bus powered
- Plug & Play
- 1 x LED indicator
- Housing material: aluminium
- Cable length without connectors: ca. 15 cm
- Colour: grey

System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 14.5 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 7
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- USB-C™ to HDMI / DisplayPort adapter

Images



General

Function:	Plug & Play
Specification:	HDCP 2.3 HDMI 1.4 HDR10
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 6.2 or above iPhone 15 Pro or above Android 14.0 or above Mac OS 14.5 or above
LED indicator:	1 x

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI / DisplayPort combo female

Technical characteristics

Maximum screen resolution:	7680 x 4320 @ 60 Hz 7680 x 4320 @ 120 Hz
Voltage supply:	USB bus powered

Physical characteristics

Housing material:	Aluminium
Cable length:	15 cm
Colour:	grey

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de