

DIGITUS® Dual vertical monitor mount, 2x 32", 2x 8 kg

DA-90438

EAN 4016032481928



Universal Dual Monitor Mount, Vertical 17-32", 8 kg max. each, clamp or grommet mount

The desktop mount allows you to mount two monitors of up to 32" / 8 kg vertically, one above the other. The mount allows you to swivel, rotate and tilt the monitors. The quick-release function enables the monitors to be attached or removed quickly. The mount offers two mounting options: both table clamp and grommet bar are included.

The desktop mount offers you the option of mounting two monitors of up to 32" / 8 kg vertically, one above the other

- Suitable for (curved) monitors up to 32" / 8 kg max.
- Quick-release fastener: VESA plate can be fixed/released with a screw when mounting and dismounting
- Height-adjustable, rotate, swivel
- VESA compatibility: 75x75, 100x100
- Integrated cable management: for an organized and tidy workspace
- Monitor holder: Tilt: -45°/+45°, swivel: -45°/+45°, front panel rotatable: -180°/+180°
- Material: steel, plastic

- Surface: Powder coating
- Monitor quantity: 2
- Two mounting options: both table clamp and feed-through bar
- Color: Black, matt
- Weight: 4.2 kg
- Tested & certified ergonomic product - Certified by IGR (Institute for Health and Ergonomics)

Attributes

- Monitor weight (max.): 8 kg
- Mounting method: Clamp-mount
- Number of monitors: 2
- Size of monitors: up to 32"
- VESA mount: 75x75 mm, 100x100 mm

Package contents

- 1x universal dual monitor holder, vertical
- 1x mounting material
- 1x assembly instructions

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	4	19.50	31.50	50.50	26.00	41,359.50
Packaging Unit Inside	1	4.88	0.00	0.00	0.00	0.00
Packaging Unit Single	1	4.88	15.30	49.60	12.30	9,334.22
Net single without Packaging	1	4.25	15.30	49.60	12.30	9,334.22

More images:



Safety notes

- Please read the entire manual before starting assembly and installation. Please contact your local dealer if you have any questions about the instructions or warnings.
- CAUTION: Use with products that exceed the permitted weight may result in damage or possible injury.
- Brackets should be fitted in accordance with the installation instructions. Incorrect installation can result in damage or injury.
- Use safety equipment and suitable tools. The product should only be installed by specialists.
- This product can be installed on timber-framed, solid concrete or stone walls.
- The load-bearing surfaces should be able to safely withstand the entire weight of appliances and all additional components.
- Only use the installation screws supplied and DO NOT TIGHTEN the screws TOO TIGHT.
- This product contains small parts that can cause a choking hazard if swallowed. Keep these parts away from children.
- Only use this product indoors. Using the product outdoors can lead to injury and damage.
- IMPORTANT: Before installation, please check all components received against the components list. If parts are damaged or missing, ask your local dealer for replacement parts.
- MAINTENANCE: Check the bracket regularly for safety and stability (preferably every three months).

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com