


300A SERIES ROCKER SWITCH



APPLICATIONS / MARKETS




Test Equipment



Computer Peripherals



Networking



Instrumentation



Telecommunication



Electrical Housewares

RoHS

SPECIFICATIONS

Contact Rating: Silver: 5A @120VAC or 28VDC;
2A @ 250VAC

Gold: 0.4VA @ 20V Max (AC or DC)

Contact Resistance: 10mΩ Max Initial

Insulation Resistance: 1,000MΩ

Dielectric Strength: 1,000V RMS at sea level

Operating Temperature: -40°C to 85°C

Contact Arrangement: SPDT, DPDT

FEATURES & BENEFITS

- Multiple rocker & paddle options
- Multiple termination options
- Sealed to IP67
- UL Listed

PART NUMBER CONFIGURATOR

Series

300A

Model No.

WSP1 - SPDT On-None-On
WSP2 - SPDT On-None-(On)
WSP3 - SPDT On-Off-On
WSP4 - SPDT (On)-Off-(On)
WSP5 - SPDT On-Off-(On)
WDP1 - DPDT On-None-On
WDP2 - DPDT On-None-(On)
WDP3 - DPDT On-Off-On
WDP4 - DPDT (On)-Off-(On)
WDP5 - DPDT On-Off-(On)

Actuator

R1 - Panel Mount
R2 - Panel Mount
R11 - Panel Mount
R16 - Panel Mount
J1 - P.C. Mount
J2 - P.C. Mount
J3 - P.C. Mount
J4 - P.C. Mount
J5 - P.C. Mount
J6 - P.C. Mount

Actuator Color

BLK - Black
RED - Red
WHT - White

Termination

M1 - Solder Lug
M2 - P.C. Mount
M3 - Quick Connect
M6 - Horizontal Rt. Angle P.C. Mount
M7 - Vertical Rt. Angle P.C. Mount
VS2 - V-Bracket P.C. Mount, Dim A=0.460
VS21 - V-Bracket P.C. Mount Dim A=0.460, Snap-In
VS3 - V-Bracket P.C. Mount, Dim A=0.630

Contact Material

Q - Silver
R - Gold

Seal

E - Epoxy Sealed

Specifications subject to change without notice 10.14.2025



E-SWITCH®


www.e-switch.com

800.867.2717

1

300A SERIES ROCKER SWITCH


SWITCH FUNCTIONS



MODEL NO.	POS. 1	POS. 2	POS. 3
WSP1	ON	NONE	ON
WSP2	ON	NONE	(ON)
WSP3	ON	OFF	ON
WSP4	(ON)	OFF	(ON)
WSP5	ON	OFF	(ON)
TERMINAL CLOSURE	2-3	OPEN	2-1

() = MOMENTARY

SINGLE POLE - SP




MODEL NO.	POS. 1	POS. 2	POS. 3
WDP1	ON	NONE	ON
WDP2	ON	NONE	(ON)
WDP3	ON	OFF	ON
WDP4	(ON)	OFF	(ON)
WDP5	ON	OFF	(ON)
TERMINAL CLOSURE	2-3, 5-6	OPEN	2-1, 5-4

() = MOMENTARY


DOUBLE POLE - DP

300A SERIES ROCKER SWITCH

PANEL MOUNT ACTUATOR



R1 ACTUATOR




R2 ACTUATOR




300A SERIES ROCKER SWITCH

PANEL MOUNT ACTUATOR



R11 ACTUATOR




R16 ACTUATOR




300A SERIES ROCKER SWITCH

PC MOUNT ACTUATOR


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



J1 ACTUATOR



J2 ACTUATOR




J3 ACTUATOR




300A SERIES ROCKER SWITCH


PC MOUNT ACTUATOR



J4 ACTUATOR



J5 ACTUATOR






J6 ACTUATOR

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS






300A SERIES ROCKER SWITCH

PANEL MOUNT TERMINATION



M1 TERMINATION - SP






M1 TERMINATION - DP






300A SERIES ROCKER SWITCH

PANEL MOUNT TERMINATION



M3 TERMINATION - SP






M3 TERMINATION - DP






ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

300A SERIES ROCKER SWITCH

PC MOUNT TERMINATION



M2 TERMINATION - SP




M2 TERMINATION - DP




300A SERIES ROCKER SWITCH

PC MOUNT TERMINATION



M6 TERMINATION - SP




M6 TERMINATION - DP




300A SERIES ROCKER SWITCH

PC MOUNT TERMINATION



M7 TERMINATION - SP



M7 TERMINATION - DP





E-SWITCH®

www.e-switch.com

800.867.2717

11



PC MOUNT TERMINATION



VS2-VS3 SP PCB MOUNTING

OPTION	DIM "A"
VS2	11.68 [.460]
VS3	16.00 [.630]

VS2-VS3 TERMINATION - SP



VS2-VS3 DP PCB MOUNTING

OPTION	DIM "A"
VS2	11.68 [.460]
VS3	16.00 [.630]

VS2-VS3 TERMINATION - DP

