Euro Plug Extension CEE7/16 male to female, 2 x 0.75 mm², 3 m, black

Description

This Euro plug extension cord by Delock is designed to reliably extend existing power connections for devices with Euro plugs (CEE 7/16). It is ideal for a wide range of applications in the home, office, or home office, and provides greater flexibility when positioning electrical devices.



Item no. 81628

EAN: 4043619816286

Country of origin: China

Package: Zip poly bag

Safe power supply with built-in child safety feature

The Euro plug is equipped with a built-in child safety feature. The special touch protection makes it difficult for foreign objects to enter the plug contacts, thereby increasing safety, especially in households with children.

Versatile and suitable for a wide range of electrical devices

The extension cord is suitable for Class II appliances with Euro plugs, such as lamps, radios, televisions, monitors, chargers, audio devices, and many other small electrical appliances. The extra cable length allows for a convenient and flexible power supply, even when outlets are farther away.

Highlights

- Euro plug (CEE 7/16) to Euro connector
- For extending power connections for Class II appliances
- Euro connector with integrated child safety lock
- Reliable and safe power transmission
- Robust and durable construction
- Flexible cable for easy installation
- Ideal for household, office, home office, and multimedia applications

Please Note

- **Caution Fire hazard!** Only use the cable for devices that do not exceed the specified load or use **power. Maximum 2.5 A – 575 W**
- Cable is not suitable for outdoor use.

Technical details

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Connectors:
  1 x 2 pin CEE7/16 male (Euro plug)
  1 x 2 pin CEE7/16 female with child safety feature (Euro plug)
- Current: max. 2.5 A
- Voltage: max. 230 V
- Performance: max. 575 W
- Cable cross section: 2 x 0.75 mm²
- Cable type: H03VVH2-F
- Cable jacket material: PVC
- Colour: black
- Length incl. connectors: ca. 3 m

Package content

- Euro plug extension

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Schnittstelle

Anschluss:	1 x 2 Pin Netzbuchse CEE7/16 mit Kindersicherung (Eurobuchse) 1 x 2 Pin Netzstecker CEE7/16 (Eurostecker)

Technische Eigenschaften

Betriebsspannung:	230 V
Maximale Leistungsaufnahme:	575 W
Maximale Stromstärke:	2,5 A

Physikalische Eigenschaften

Kabeltyp:	H03VVH2-F
Kabellänge inkl. Anschlüsse:	3 m
Material:	PVC
Farbe:	schwarz

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**