

BW 2056T/E

Tool case with assortment of 163 GENERAL MAINTENANCE TOOLS

1/4" 12"

- Adjustable telescopic handle
- Removable interior tool panel
- Integrated soft foam tray

465x330x225 mm

	Art.
020566120	BW 2056T/E

- n. 12 **BW 42:** Combination wrenches 8-9-10-11-12-13-14-15-16-17-18-19 mm
- n. 6 **1201E:** 2,5x50 - 3x75 - 4x125 - 5,5x150 - 6,5x150 - 8x150 mm
- n. 9 **BW 96BPC/SC9:** Set of 9 ball head offset hexagon key wrenches 1,5-2-2,5-3-4-5-6-8-10 mm
- n. 2 **1202E:** PH1x80 - PH2x100 mm
- n. 1 **BW 1253:** Mains testing screwdriver 3,5x100 mm
- n. 1 **BW 111:** Adjustable wrenches 250 mm
- n. 1 **BW 1048:** Slip joint pliers, boxed joints 250 mm
- n. 2 **1209E/PZ:** PZ1x80 - PZ2x100 mm
- n. 22 **BW 1256/C21-1:** Micro screwdriver with 21 interchangeable inserts 4 mm and handle
- n. 1 **BW 1128BMX:** Electrician's scissors, stainless steel blades, with microteeth 145 mm
- n. 1 **BW 1370 300:** Engineer's hammers 300 g
- n. 1 **BW 1692/5:** Measuring tapes 5 m
- n. 1 **BW 1082BM:** Diagonal cutting nippers 160 mm
- n. 1 **BW 1150BM:** Heavy-duty combination pliers 180 mm
- n. 1 **BW 1166BM:** Extra-long needle knurled nose pliers 160 mm
- n. 1 **BW 1725CR:** Mini hacksaw frame 150 mm
- n. 1 **1771:** 18 mm
- n. 61 **BW 861/C61:** Set of 60 bits with magnetic bit holder, in pocket-size case
- n. 1 **BW 895/1:** Socket holders for items BW 861, BW 862, BW 866
- n. 13 **BW 900:** Hexagon hand sockets, 1/4" 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 1 **BW 900/20:** Extension cords - 1/4" 50 mm
- n. 1 **BW 900/20L:** Extension cords - 1/4" 100 mm
- n. 1 **BW 900/25:** Universal joint - 1/4"
- n. 1 **BW 900/30:** 1/4" drive spinner handle
- n. 1 **BW 900/42:** 1/4" drive sliding T-handle 110 mm
- n. 13 **BW 920A:** Hexagon hand sockets, 1/2" 10-11-12-13-14-15-16-17-18-19-21-22-24 mm
- n. 1 **BW 920/21:** Extension bar - 1/2" 125 mm
- n. 1 **BW 920/25:** Universal joint, 1/2"
- n. 1 **BW 910/16F:** Adaptor - F3/8"xM1/2"
- n. 1 **BW 920/22:** Extension bar - 1/2" 250 mm
- n. 1 **900E/55:** 126 mm
- n. 1 **920E/55:** 264 mm



Scan the QR Code to access the web tab

Specs, media and documentation in one click.

