Data and charging cable USB Type-C™ to Lightning™ for iPhone™, iPad™ and iPod™ grey 0.5 m MFi

Description

This USB data and charging cable by Delock can be used to connect an iPhone™, iPad™ or iPod™ to a computer or laptop with USB Type-C™ or Thunderbolt™ 3 port, e.g. to a MacBook. The device is charged and data can be transferred.
The connection between Apple and Android devices is also possible.



Item no. 86630

EAN: 4043619866304

Country of origin: China

Package: Retail Box

Fast Charge Support

With fast charge support, compatible Apple devices can also be connected to a USB Type-C™ PD charger for especially quick charging.

MFi Certified

The MFi certification and the original Apple C94 connector guarantee full compatibility to all devices with Lightning™ connector.

Technical details

- Connectors:
  1 x USB Type-C™ male >
  1 x Apple Lightning™ male
- MFi certified cable with original Apple C94 connector
- Compatible to iPhone, iPad, iPod
- Supports fast charge function (ex iPhone 8 / iPad Pro)
- Cable gauge:
  30 AWG data line
  22 AWG power line
- Voltage: up to 9 V
- Output current: up to 3 A
- Cable diameter: ca. 3.2 mm
- Copper conductor
- Connector with metal housing
- With nylon braid
- Data transfer rate up to 480 Mbps
- Colour: grey
- Length incl. connectors: ca. 0.5 m

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

System requirements

- PC or laptop with a free USB Type-C™ or Thunderbolt™ 3 port or
- Charger with a free USB Type-C™ port
- Device with a free Lightning™ port

Package content

- USB-C™ to Lightning™ cable

Images





All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Cable finishing:	Nylon braid
Specification:	USB 2.0

Interface

Connector 1:	1 x USB 2.0 Type-C™ male
Connector 2:	1 x Apple Lightning™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	28 AWG data line 22 AWG power line
Length:	0.50 m
Colour:	grey
Cable diameter:	3.7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**