

# USB 3.0 Dual Band WLAN ac/a/b/g/n Stick 867 + 300 Mbps

## Description

This wireless LAN USB stick can be connected to a computer for the connection to a WLAN network. The WLAN stick can be connected to an AccessPoint (HotSpot) or WLAN-router in a 2.4 GHz and 5 GHz band. Furthermore it enables an adhoc connection to a second computer.



**Item no. 12463**

EAN: 4043619124633

Country of origin: China

Package: Retail Box

## Technical details

- Connector: 1 x USB 3.0 Type-A male
- Chipset: Realtek RTL8812AU
- 2T2R mode with 867 Mbps @ 5 GHz and 300 Mbps @ 2.4 GHz
- Frequency range: 2.4 GHz + 5 GHz band
- Antenna gain: 2 dBi
- Antenna type: PCB / PIFA
- Compatible with IEEE 802.11ac/a/n/b/g
- Encryption WEP, WPA, WPA2
- Transmission power (EIRP): 100 mW
- Supports DFS (Dynamic Frequency Selection)
- WPS button
- Dimensions (LxWxH): ca. 73 x 23 x 10 mm


## System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-A port

## Package content

- WLAN USB stick
- Driver CD
- User manual

## Images



## Interface

|            |                            |
|------------|----------------------------|
| Connector: | 1 x USB 5 Gbps Type-A male |
|------------|----------------------------|

## Technical characteristics

|                     |                                                      |
|---------------------|------------------------------------------------------|
| Chipset:            | Realtek RTL8812                                      |
| Data transfer rate: | 867 Mbps @ 5 GHz @ 2T2R<br>300 Mbps @ 2.4 GHz @ 2T2R |
| Frequency range:    | 2.4 GHz band<br>5 GHz band                           |
| Gain:               | 2 dBi                                                |
| Transmission power: | 100 mW                                               |
| Encryption:         | WEP<br>WPA<br>WPA2                                   |
| WLAN standard:      | 802.11ac<br>802.11n<br>802.11a<br>802.11b<br>802.11g |

## Physical characteristics

|               |             |
|---------------|-------------|
| Antenna type: | PIFA<br>PCB |
| Length:       | 73 mm       |
| Width:        | 23 mm       |
| Height:       | 10 mm       |
| Colour:       | black       |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |

E-Mail

[info@delock.de](mailto:info@delock.de)

Website

[www.delock.de](http://www.delock.de)

