



LogiLink®


Universal Travel Adapter 70 W PD

2x USB-A, 1x USB-C, 1x AC Outlet
1x USB-C Cable

Art. No.: PA0357

One Adapter, Every Destination!

All-in-one travel adapter includes 4 different plugs that cover over 200 countries. Also include 2 USB-A, 1 USB-C ports and 1 USB-C cable for fast charging smartphones, laptops, tablets, power banks and more.



Universal
AC Outlet



PD 65W &
QC 60W



Power
5 Devices



Spare Fuse
Included




Fireproof
Material



Compact &
Lightweight

Universally Compatible with **200+** Countries

Designed with 4 interchangeable plugs that can be adapted to outlets in several countries, including plugs in the EU, UK, USA and Australia, covering more than 200 countries and regions.



International outlet adapter accepts 10 types of plugs, use it both domestically and abroad.



Type A



Type B



Type C



Type E



Type F



Type G



Type I



Type J



Type L



Type N



Universal AC outlet

Versatile Charging

Supports 2x USB-A QC 3.0, 1x USB-C PD 3.0, an AC outlet and a built-in USB-C cable. Perfect for powering multiple devices simultaneously, ensuring you always have a cable on hand for charging.

GaN Technology

Compact design with advanced GaN technology for efficient, high-power performance and better heat management.

LED indicator

USB-A1 QC 3.0 Port
USB-A2 QC 3.0 Port

USB-C2 PD 3.0 port

USB-C1 PD 3.0 cable



PA0357



Made in China



*Adapter (AC-AC) does not convert voltage.


*Do not use with appliances requiring ground wire.

*The specifications and pictures are subject to change without prior notice.

*All trade names referenced are the registered trademarks of their respective owners.

70 W PD Fast Charging

Delivers up to 70 W Power Delivery (PD) via the USB ports. Easily charge your laptops, smartphones, and other high-powered devices.



Enhanced Safety

Made of fire-resistant material with built-in 10 A fuse, safety shutters, and multiple charging protections for reliable use.




Portable Design

Lightweight and space-saving, perfect for travel.

Wide Applications

Great for travelers, remote workers, and students. Powers smartphones, tablets, laptops, and small appliances with ease.



*Adapter (AC-AC) does not convert voltage.
*Do not use with appliances requiring ground wire.
*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



PA0357



Made in China

Specification:

Input	100–250 V AC 50/60 Hz 10 A, 2500 W max.
Output Interface	1x USB-C female, 1x USB-C male, 2x USB-A female, 1x AC outlet
USB Output	USB-C1/C2: 5 V/3 A (15 W), 9 V/3 A (27 W), 12 V/3 A (36 W), 15 V/3 A (45 W), 20 V/3.25 A (65 W max.) USB-A1: 5 V/1 A (5 W) USB-A2: 4.5 V/5 A (22.5 W), 5 V/4.5 A (22.5 W), 5 V/3 A (15 W), 9 V/3 A (27 W), 12 V/3 A (36 W), 20 V/3 A (60 W max.) PPS: 3.3–11 V/3 A (33 W max.), 3.3–11 V/5 A (55 W max.) C1+C2: 45 W+20 W, C1+A1: 60 W+5 W, C1+A2: 45 W+20 W C2+A1: 65 W+5 W, C2+A2: 45 W+15 W, A1+A2: 5 W+60 W C1+C2+A1: 45 W+20 W+5 W, C1+(C2+A2): 45 W+(15 W), C1+A1+A2: 45 W+18 W+5 W, (C2+A2)+A1: (15 W)+5 W C1+(C2+A2)+A1: 45 W+(15 W)+5 W Total output: 70 W max.
Efficiency	Level VI
LED Indicator	Blue
Protections	Overcharge, overcurrent, overheat, overvoltage, overload and short circuit
Operating Temperature	-10–35°C
Operating Humidity	20–80% RH (no-condensation)
Color	White
Dimensions	9 x 5.5 x 5.4 cm
Weight	237 g
Cable Length	70 cm

Package Contents:

- » 1x Travel Adapter
- » 1x User Manual

Package Information:

- » Packing Dimension: 98 x 60 x 70 mm
- » Packing Weight: 0.252 kg
- » Carton Dimension: 320 x 300 x 290 mm
- » Carton Q'ty: 48 pcs
- » Carton Weight: 13.9 kg



*Adapter (AC-AC) does not convert voltage.
*Do not use with appliances requiring ground wire.
*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

