

Łącznik ZM-180

Nr ref C28075N00

Ref. arch 40693

NOWOŚĆ



PRZEZNACZENIE PRODUKTU

- łączenie opraw w ciągu, pod kątem 180 stopni

MONTAŻ

- do profilu, za pomocą zamka małego i docisków (w zestawie)

SPECYFIKACJA TECHNICZNA

Materiał	stal nierdzewna
Kolor	 srebrny
Grubość	1.2 mm

Odporność na korozję	tak
Kąt łączenia	180°

PROFILE POWIĄZANE > ARCHITEKTONICZNE



LOC-30

A18015

Ref. arch 18015



3035

A18039


Ref. arch 18039



KOZMA

A18040

Ref. arch 18040



4050

A18050

Ref. arch 18050



4050-W

A18051

Ref. arch 18051



LARKO

A05552

Ref. arch B5552



LOKOM

A05553

Ref. arch B5553



LIPOD

A05554

Ref. arch B5554



GIZA

A05556

Ref. arch B5556



OPAC-30

A06164

Ref. arch B6164

Łącznik ZM-180


Nr ref C28075N00

Ref. arch 40693


KLUŚ Inspiring
Solutions



KOPRO
A06367
Ref. arch B6367



KOZEL
A06454
Ref. arch B6454




KOZUS
A07823
Ref. arch B7823



KOPRO-30
A07890
Ref. arch B7890



3035-O
A08441
Ref. arch B8441



JAZ
A08547
Ref. arch B8547



OPK-4
A00370
Ref. arch C0370



KOZUS-CR
A00600
Ref. arch C0600



GIZA-LL
A00758
Ref. arch C0758



PDS-T
A02057
Ref. arch C2057



GIZA-DUO-LL
A02162
Ref. arch C2162



GIZA-LL-T
A02479
Ref. arch C2479



GLAZA-LL
A02627
Ref. arch C2627



GIZA-LL-UST
A02724N
Ref. arch C2724



PDS-UST
A02725
Ref. arch C2725



GLAZA-DUO
A03059
Ref. arch C3059



DIPOKET
A01177
Ref. arch H1177



POKET
A01179
Ref. arch H1179



DIPOK-US
A01233
Ref. arch H1233

PROFILE POWIĄZANE > DO BUDOWY KINKIETÓW

Łącznik ZM-180

Nr ref C28075N00

Ref. arch 40693

KLUŚ Inspiring
Solutions



WERKIN

A18025


Ref. arch 18025



KIDES

A18031

Ref. arch 18031



KIDES-DUO

A18032


Ref. arch 18032



LIT-L

A18033

Ref. arch 18033



OBIT

A04826

Ref. arch W4826



PLAKIN-DUO

A04106


PROFILE POWIĄZANE > DO OŚWIETLENIA GŁÓWNEGO



MOD-50

A18047


Ref. arch 18047



MOD-100

A18049A

Ref. arch 18049



SEPOD

A06593


Ref. arch B6593



SEKOMA

A06595

Ref. arch B6595



SEKODU

A06597


Ref. arch B6597



LARKO-50

A00756


Ref. arch C0756



KOZEL-50

A00757


Ref. arch C0757



KOZUS-50

A00958

Ref. arch C0958



LIPOD-50

A02609

Ref. arch C2609

PROFILE POWIĄZANE > FASADOWE

Łącznik ZM-180

Nr ref C28075N00

Ref. arch 40693

KLUŚ Inspiring
Solutions

NOWOŚĆ



FASKO

A04323

Ref. arch C4323

PROFILE POWIĄZANE > MINIMALISTYCZNE



PIKO-ZM

A01168

Ref. arch C1168



KOZEL-10

A01575

Ref. arch C1575

PROFILE POWIĄZANE > PODŚWIETLENIE NISZ



NISA-KRA

A18026

Ref. arch 18026



NISA-KON

A18027

Ref. arch 18027



NISA-NI

A18029

Ref. arch 18029

PROFILE POWIĄZANE > PROFILE TECHNICZNE



TPK-4

A18044

Ref. arch 18044



TEPIKO

A18046

Ref. arch 18046



RAM-KOZE-50

A18055

Ref. arch 18055



RAM-3035-KOZE

A18056

Ref. arch 18056



RAM-KOZE-100

A18057

Ref. arch 18057

Łącznik ZM-180

Nr ref C28075N00

Ref. arch 40693

KLUŚ Inspiring
Solutions



RAM-TEK-50

A18059

Ref. arch 18059



RAM-KOL-50

A18060

Ref. arch 18060



RAM-TEK-100

A18061


Ref. arch 18061



RAM-KOL-100

A18062

Ref. arch 18062



TEKNIK-ZM

A00399

Ref. arch C0399



TEKUS-ZM

A01293


Ref. arch C1293



TEKNIK-ZM-TK

A01554


Ref. arch C1554



MOD-KR-KOZE

A01772

Ref. arch C1772



3035-KR-KOZE

A01780

Ref. arch C1780



HR-MAX-TW

A01828

Ref. arch C1828



HR-MAX-T

A01827


Ref. arch C1827



MOD-KR-TEK

A02052

Ref. arch C2052



MOD-KR-KOL

A02053

Ref. arch C2053

PROFILE POWIĄZANE > SUFITY NAPINANE



FOLED

A08332V1


Ref. arch B8332V1



FOLED-SUF

A08333V1

Ref. arch B8333V1



FOLED-BOK

A08334V1


Ref. arch B8334V1



FOLED-50-SUF

A03631

Ref. arch C3631



FOLED-50

A03632

Ref. arch C3632


Łącznik ZM-180

Nr ref C28075N00

Ref. arch 40693

KLUŚ Inspiring
Solutions

NOWOŚĆ



FOLED-50-BOK

A0A57945

Ref. arch SA57945

PROFILE POWIĄZANE > UNIWERSALNE



PAC-ALU

A04370

Ref. arch B4370



KUBIK-45

A07697

Ref. arch B7697



OLEK

A08505

Ref. arch B8505



PDS-ZMG

A01418

Ref. arch C1418



PDS-ZM-PLUS

A02056

Ref. arch C2056