

CHARX T2CCS-MFC-M4X10-BIT - Repair kit



1582285

<https://www.phoenixcontact.com/gb/products/1582285>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect standard, CCS type 2, Repair kit, Accessories, housing: black, with replaceable mating face frame, with 5x M4X10 flat-head screws with Torx safety drive (IPR TORX PLUS®), with special bit (867/4 IPR TORX PLUS® bit, 20 IPR x 89 mm) for insulated screwdriver, With integrated front part of the DC contacts, for replacement of the mating face frame of vehicle charging connectors, IEC 62196-3

Product description

Repair kit with replaceable mating face frame for CCS type 2 DC vehicle connector

Commercial data

Item number	1582285
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	XWBMHY
Product key	XWBMHY
GTIN	4067923075719
Weight per piece (including packing)	277.8 g
Weight per piece (excluding packing)	250 g
Customs tariff number	85444290
Country of origin	PL

CHARX T2CCS-MFC-M4X10-BIT - Repair kit



1582285

<https://www.phoenixcontact.com/gb/products/1582285>

Technical data

Product properties

Product type	Repair kit
Product family	CHARX connect standard
Type	Accessories
Design	with replaceable mating face frame
	with 5x M4X10 flat-head screws with Torx safety drive (IPR TORX PLUS®)
	with special bit (867/4 IPR TORX PLUS® bit, 20 IPR x 89 mm) for insulated screwdriver
	With integrated front part of the DC contacts
Charging standard	CCS type 2
Charging mode	Mode 4

Material specifications

Color (Housing)	black (9005)
Color (Handle area)	black (9005)
Color (Mating face)	black (9005)
Color (Protective cap)	black (9005)
Color (Cable)	black (9005)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 40 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

Standards and regulations

Standards

Standards/regulations	IEC 62196-3
-----------------------	-------------

CHARX T2CCS-MFC-M4X10-BIT - Repair kit



1582285

<https://www.phoenixcontact.com/gb/products/1582285>

Classifications

ECLASS

ECLASS-13.0	27144792
ECLASS-15.0	27144792

ETIM

ETIM 10.0	EC002884
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CHARX T2CCS-MFC-M4X10-BIT - Repair kit



1582285

<https://www.phoenixcontact.com/gb/products/1582285>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk