

# External USB 2.0 Sound Adapter Virtual 7.1 - 24 bit / 96 kHz with S/PDIF

## Description

The USB sound adapter by Delock expands the computer with an additional sound card. Headphones or speakers can be connected. The audio output has a combo connector and can be used as a conventional analog stereo output or as an optical digital (S/PDIF) output. The adapter can playback audio files with up to 24 bit / 96 kHz.



**Item no. 63926**

EAN: 4043619639267

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 2.0 Type-A male >
  - 1 x 3.5 mm 3 pin stereo jack female microphone
  - 1 x 3.5 mm 3 pin stereo jack female (analogue) / S/PDIF (digital) speaker
- Chipset: C-Media CM6533
- Functional keys: Volume-UP, Volume-Down, Mute
- USB audio device specification 1.0
- Up to 24 Bit / 96 kHz sampling rate for playback and 16 Bit / 48 kHz for recording
- Supports virtual 7.1 channel Sound
- USB bus powered
- Plug & Play

## System requirements

- Chrome OS 61.0 or above
- Mac OS 10.9 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

## Package content

- USB sound adapter

## Images



## General

|                             |                                                                                                                                                                               |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Function:                   | Plug & Play                                                                                                                                                                   |
| Specification:              | USB 2.0                                                                                                                                                                       |
| Supported operating system: | Chrome OS 61.0 or above<br>Mac OS 10.9 or above<br>Windows 10 32-Bit<br>Windows 10 64-Bit<br>Windows 7 32-Bit<br>Windows 7 64-Bit<br>Windows 8.1 32-Bit<br>Windows 8.1 64-Bit |

## Interface

|              |                                                                                   |
|--------------|-----------------------------------------------------------------------------------|
| Connector 1: | 1 x USB 2.0 Type-A male                                                           |
| Connector 2: | 1 x 3.5 mm 3 pin stereo jack female microphone                                    |
| Connector 3: | 1 x speaker 3.5 mm stereo jack female (analogue) output / S/PDIF (digital) output |

## Technical characteristics

|          |                |
|----------|----------------|
| Chipset: | C-Media CM6533 |
|----------|----------------|

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |