



GRINDING WHEELS

A96 GREY CORUNDUM

C49 GREEN
SILICON CARBIDE

dimensions	grains						grain	
Ø x thickness x hole	24	36	46	60	80	100		
75 x 10 x 10				A96.053	A96.078	A96.102	C49.010	
75 x 12 x 13				A96.054	A96.079	A96.103	C49.011	
100 x 10 x 13				A96.055	A96.080	A96.104		
100 x 13 x 13		A96.204	A96.209	A96.056	A96.214	A96.105	C49.012	
100 x 15 x 13	A96.199	A96.205	A96.210	A96.057	A96.082	A96.106	C49.013	
100 x 20 x 13	A96.200	A96.206	A96.211	A96.058	A96.083	A96.107	C49.050	
125 x 13 x 16		A96.157	A96.166	A96.175	A96.185	A96.191		
125 x 15 x 16	A96.149	A96.158	A96.167	A96.176	A96.186	A96.192	C49.034	
125 x 20 x 16	A96.150	A96.127	A96.168	A96.177	A96.187	A96.193	C49.035	
125 x 25 x 16	A96.151	A96.160	A96.169	A96.178	A96.188	A96.194		
150 x 16 x 16	A96.001	A96.019	A96.038	A96.063	A96.088	A96.112	C49.051	
150 x 20 x 16	A96.002	A96.020	A96.039	A96.064	A96.089	A96.113	C49.016	
150 x 20 x 32		A96.207		A96.212				
150 x 25 x 16	A96.003	A96.021	A96.040	A96.065	A96.090	A96.114	C49.017	
150 x 30 x 16	A96.004	A96.022	A96.041	A96.066	A96.091	A96.115		
175 x 20 x 20	A96.005	A96.023	A96.042	A96.067	A96.092	A96.116	C49.018	
175 x 25 x 20	A96.006	A96.024	A96.043	A96.068	A96.093	A96.117	C49.052	
200 x 20 x 20	A96.008	A96.026	A96.045	A96.070	A96.095	A96.119	C49.019	
200 x 20 x 32		A96.208		A96.213				
200 x 25 x 20	A96.009	A96.027	A96.046	A96.071	A96.096	A96.120	C49.020	
200 x 30 x 20	A96.010	A96.028	A96.047	A96.072	A96.097	A96.121	C49.053	
250 x 25 x 25	A96.011	A96.029	A96.048	A96.073	A96.098	A96.122	C49.054	
250 x 30 x 25	A96.012	A96.030	A96.049	A96.074	A96.099	A96.123	C49.055	
300 x 30 x 30	A96.013	A96.031	A96.050	A96.075	A96.100	A96.124		
300 x 35 x 30	A96.147	A96.155	A96.164	A96.173	A96.182			
300 x 40 x 30	A96.014	A96.032	A96.051	A96.076	A96.101			
400 x 50 x 40	A96.148	A96.033	A96.052	A96.077	A96.184			

TWO SIDE TAPERED WHEELS - grain 80



dimensions	A96 grey corundum		A99 white corundum		dimensions	A96 grey corundum		A99 white corundum	
Ø x thickness x hole	ref.		ref.		Ø x thickness x hole	ref.		ref.	
125 x 6 x 16	A96C.01		A99C.01		175 x 8 x 20	A96C.08		A99C.08	
125 x 7 x 16	A96C.02		A99C.02		175 x 10 x 20	A96C.09		A99C.09	
125 x 8 x 16	A96C.03		A99C.03		200 x 6 x 20	A96C.10		A99C.10	
150 x 6 x 16	A96C.04		A99C.04		200 x 8 x 20	A96C.11		A99C.11	
150 x 7 x 16	A96C.05		A99C.05		200 x 10 x 20	A96C.12		A99C.12	
150 x 8 x 16	A96C.06		A99C.06		200 x 12 x 20	A96C.14			
150 x 10 x 16	A96C.13		A99C.13		250 x 10 x 25	A96C.15			
175 x 6 x 20	A96C.07		A99C.07		250 x 13 x 25	A96C.16			

☐ PG pack

☐ neutral pack
Packing: pcs.