

USB 20 Gbps extension cable angled left / right USB PD 3.1 Extended Power Range 240 W 2 m

Description

This USB extension cable by Delock enables the connection of various devices, such as smart phones, monitors, external enclosures and docking stations, via a USB Type-C™ or Thunderbolt™ 3 port of a PC or laptop. The cable supports the transfer of USB as well as DisplayPort and PCI Express data.

USB4™ 20 Gbps

The cable enables data transfer rates up to 20 Gbps when connecting USB4™-compatible devices. Of course, USB 3.2 or USB 2.0 devices can also be connected.

USB Power Delivery (USB PD 3.1) support up to 240 watt

Support for the Extended Power Range resp. USB Power Delivery 3.1 standard means that connected devices can be supplied with power, up to 240 W (48 V / 5 A) is possible.



Item no. 81148

EAN: 4043619811489

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 20 Gbps USB Type-C™ male
 - 1 x USB 20 Gbps USB Type-C™ female
- Downwards compatible to USB 3.2, USB 2.0 and Thunderbolt™ 3
- Chipset: E-Marker
- Cable gauge:
 - 32 AWG data line
 - 30 AWG power line
- Cable diameter: ca. 5 mm
- Data transfer rate up to 20 Gbps
- Display resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- Supports PCI Express 3.0 protocol
- Supports DisplayPort 1.4a protocol
- Supports DisplayPort Alt Mode 2.0
- Dual channel, bi-directional data transfer
- Supports Extended Power Range (EPR)
- USB Power Delivery (USB PD 3.1) support up to 240 watt (48 V / 5 A)

- Colour: black
- Length incl. connectors: ca. 2 m

Package content

- USB 20 Gbps cable

Images



General

Specification:	DisplayPort 1.4 HDCP 1.4 HDCP 2.3 HDR10 PCI Express 3.0 USB 20 Gbps USB Power Delivery 3.1
----------------	--

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ female

Technical characteristics

Data transfer rate:	20 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Housing material:	Aluminium
Cable gauge:	32 AWG data line 30 AWG power line
Length:	2 m
Colour:	black
Cable diameter:	5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de