



USB 2.0 A to Lightning Cable

Made for iPhone/iPad/iPod

USB 2.0 A to Lightning Cable



MFi
certified



2.4A max



For iOS devices




C89 Module

MFi Certificated Supplier

Made for

🍏 iPhone | iPad | iPod



WHY Choosing MFi Certificated Supplier

iOS

Totally compatible for iOS devices



Supports Apple's official warranty policy




Safeguard your battery while charging



Stable and safe voltage

Apple Officially Certifiable

UPC/EAN codes available on the Apple website



Original Apple MFi Chip

Upgraded Apple C89 module , ensures safer & smarter charging environment



Note: The internal structure is a rendering
please refer to the actual product

Fast Charge for iPhone

MFi certified, up to 2.4A current



480Mbps Fast Data Transmission

Standard USB 2.0, simultaneous fast charge and transfer



Upgraded Apple C89 Connector

Ensure charging faster and safer

13mm extra long tail

Long service time

Aluminum alloy shell


Good texture



Note: All data are from Vention Lab

Durable and Not Easy to Get Knotted

TPE+Nylon braided jacket, wear-resistant
and resistant to stretch



No Warning Pop-up

Synchronized with updated system
fully compatible with iOS



MFi Certified Cable,
Fully compatible with iOS



Non-MFi Certified Cable,
Unstable and incompatible

Reasons for Pop-ups

Not equipped with
Apple chip and
cannot compatible
with iOS, so as to
pop up a warning

Non-MFi Hazard

No Apple chip to filter
dangerous currents
and data which may
damage the phone

Universal Compatibility

Fully compatible with iOS system

iPhone

iPhone 12 mini
iPhone 12
iPhone 12 Pro
iPhone 12 Pro Max
iPhone SE2
iPhone 11 Pro Max
iPhone 11 Pro
iPhone 11
iPhone Xs
iPhone Xs Max
iPhone X
iPhone XR
iPhone 8
iPhone 8 Plus
iPhone 7
iPhone 7 Plus
iPhone SE
iPhone 6s
iPhone 6s Plus
iPhone 6
iPhone 6 Plus
iPhone 5s

iPad

iPad Pro 10.5 "
iPad Pro 12.9 "
iPad Pro 9.7 "
iPad Air 3
iPad Air 2
iPad Air
iPad 5
iPad 6
iPad 7
iPad mini 5
iPad mini 4
iPad mini 3
iPad mini 2

iPod

iPod touch 6
iPod touch 7



Product Parameters

Brand: Vention

Name: USB 2.0 A to Lightning Cable

Model: LABR

Color: Red

Interface: USB 2.0 A Male/Lightning Male

Module Model: C89 (Lightning Connector+Chip)

Interface Technics: Nickel-plated

Transmission Speed: 480Mbps

Conductor: Tinned-copper

Shell: Aluminum Alloy

Shielding: Aluminum Foil+Metal Braided

Jacket: TPE+Nylon Braided Jacket

AWG: 1m: 24+30AWG, 1.5-2m: 21+30AWG

OD: 3.5mm

Length: 1/1.5/2m

Power Supply: 2.4A

Warranty: 1 Year

Packing: Color Box



Note: Packing difference exists for different meters or batches
The photo is for reference only

