

USB 3 in 1 Retractable Charging Cable Type-A to Micro USB / 2 x USB Type-C™ with Fast Charging white

Description

This practical 3 in 1 retractable cable by Delock can be connected to a power source with USB-A connection and can be used to charge single devices with Micro USB or USB Type-C™ interface.

Useful companion

This cable is the ideal companion for on the go e.g. on business trips or on holidays, since it combines the two most common interfaces in one cable for the latest mobile devices. This avoids annoying cable clutter and unnecessary carrying around of countless cables.

Fast charging and power

One of the two USB Type-C™ ports enables the data transfer as well as **fast charging** with a power bank or modern USB chargers. The other two connectors can be used for charging only.

Flexible

The charging cable can be pulled out in five stages and thus offers different cable lengths, depending on requirements.



Item no. 85358

EAN: 4043619853588

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB Type Micro-B male (charging only)
 - 1 x USB Type-C™ male (charging only)
 - 1 x USB Type-C™ male (Fast Charging + data transfer)
- Maximum output current: 3 A
- Voltage: max. 5 V
- Fast Charging function: 10 V / 2.4 A
- Data transfer rate up to 480 Mbps
- Cable gauge: 22 AWG
- Flat cable
- Contacts gold-plated
- Colour: white / silver / green / blue
- Length incl. connectors: ca. 113 cm (total incl. housing)

retracted:
USB-A Host-cable ca. 2.5 cm
3 Device-cable ca. 14.5 cm
extended:
USB-A Host-cable ca. 45 cm
3 Device-cable ca. 59 cm


System requirements

- Power source with a free USB Type-A port
- PC or laptop with a free USB Type-A port

Package content

- Cable

Images



General

Style:	Flat cable
--------	------------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type Micro-B male 2 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	2.4 A 3 A
Voltage:	5 V 10 V

Physical characteristics

Connector finishing:	gold-plated
Cable gauge:	22 AWG
Length:	1.13 m
Colour:	blue green white silver

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

