

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0541045033

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 50 Circuits, Tin-Silver-Bismuth Plating



Documents:	
Drawing (PDF)	Product Guide (PDF)
Product Specification PS-54104-073-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification SPK-54104-001-001 (PDF)	Reference Guide (PDF)
Datasheet (PDF)	

Agency Certification	
CSA	LR19980
General	
Product Family	FFC/FPC Connectors
Series	54104
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
Taxonomy	FFC / FPC Connectors
UPC	887191257846
Physical	
Actuator Type	Slider
Circuits (Loaded)	50
Color - Resin	Natural
Contact Position	Top
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	2.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Silver-Bismuth
Material - Plating Termination	Tin-Silver-Bismuth
Material - Resin	Nylon
Net Weight	555.300/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

54104 Series

Mates With

Premo-Flex FFC Cable [15166](#) , [98266](#) , [15266](#) , [15366](#)

Reference - Drawing Numbers

Packaging Specification	SPK-54104-001-001
Product Specification	PS-54104-073-001
Sales Drawing	SD-54104-083-001, SD-54104-084-001, SD-54104-084-002

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION