

DIGITUS® Vertical Notebook Stand

DA-90439

EAN 4016032481799



Vertical Notebook Stand, aluminum silver

The vertical notebook stand from DIGITUS® offers a compact solution for positioning your notebook in your workspace. This also optimally enables the cooling of your device. Timeless, elegant aluminum design blends seamlessly with any environment. Silicone pads on the inside protect your notebook and ensure firm support. The holder can be adjusted between 7.7 and 40 mm. Anti-slip pads on the bottom ensure a secure hold. The maximum load capacity is 10 kg.

Compat solution for positioning your notebook in your workspace - enables optimal cooling for your device

- Elegant aluminum
- Variable size: 7.7 - 40 mm - Universal solution for notebooks of all kinds
- Maximum load capacity: 10 kg

- Anti-slip pads for secure positioning
- Silicone pads on the inside protect your notebook
- Save space when positioning your notebook on your desk
- Enables optimal cooling of your device thanks to vertical positioning
- Dimensions: 9.2 (D) x 15 (W) x 4.3 (H) cm
- Weight: 407 g
- Color: Silver
- Material: Aluminum

Attributes

- Style: Notebook Workstation



Package contents

- Vertical Notebook Stand
- Mounting material
- QIG

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	20	10.20	27.00	35.00	23.00	21,735.00
Packaging Unit Inside	1	0.51	5.00	9.70	15.50	751.75
Packaging Unit Single	1	0.51	5.00	9.70	15.50	751.75
Net single without Packaging	1	0.46	5.00	9.70	15.50	751.75

A minimalist desk setup featuring a large monitor, a keyboard, a mouse, a small potted plant, and a pencil holder, all on a light-colored surface against a white brick wall.



- Please read the entire manual before starting assembly and installation. Please contact your local dealer if you have any questions about the instructions or warnings.
- CAUTION: Use with products that exceed the permitted weight may result in damage or possible injury.
- Brackets should be fitted in accordance with the installation instructions. Incorrect installation can result in damage or injury.
- Use safety equipment and suitable tools. The product should only be installed by specialists.
- This product can be installed on timber-framed, solid concrete or stone walls.
- The load-bearing surfaces should be able to safely withstand the entire weight of appliances and all additional components.
- Only use the installation screws supplied and DO NOT TIGHTEN the screws TOO TIGHT.
- This product contains small parts that can cause a choking hazard if swallowed. Keep these parts away from children.
- Only use this product indoors. Using the product outdoors can lead to injuries and damage.
- IMPORTANT: Before installation, please check all components received against the components list. If parts are damaged or missing, ask your local dealer for replacement parts.
- MAINTENANCE: Check the bracket regularly for safety and stability (preferably every three months).

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH

Auf dem Schüffel 3

Lüdenscheid, Germany

<https://www.assmann.com>

info@assmann.com