



PD 20W for New iPhone 13

With PD fast charging protocol and MFi certificated charging cable, save your charging time




Note: All data are from Vention Lab

Three Times Faster

Comparing to the original 5W charger,
lift your charging speed to 3 times




iPhone13
30min charging test



Note: All data are from Vention Lab

PD Certification Chip

Adopted with PD certificated chip,
intelligently identify multiple charging protocols



PD

PD certificated
Intelligent charging

MFi

MFi Apple certificated
chip No pop-up

Note: This product is not equipped with cable, customers are recommended to purchase Vention MFi certificated PD fast charge cable. The internal structure is rendering, please refer to the actual product

Multiple Protocols Compatible

Support Apple, Huawei, Xiaomi, Samsung,
OPPO, vivo phone, tablet and earphone devices




PPS | PD3.0 | QC4.0 | AFC | FCP | BC1.2 | Apple 2.4A

Charging Safety Guarantee

When battery reaches 80%, automatically switch to trickle charging mode for safe charging status



Safe charging graph



Note: All data are from Vention Lab

Excellent Temperature Control

With high performance transformer MOS tube, capacitance,
etc., ensures a safe and low-temperature charging



Note: The internal structure is a rendering,
please refer to the actual product

Premium Shell Material

Tough PC fire retardance shell with features of high temperature durability, anti-pressure, and fire durability



High
temperature
durability



Anti
pressure



Fire
retardance



Tiny and Portable

Easy to carry around



Six Major Protections



Over-pressure
protection



Over-current
protection



Circuit
protection



Short-circuit
protection




Over temperature
protection



Thunder
protection

Product Parameters

Brand:	Vention
Name:	Fast Charger
Model:	FADB0-EU
Color:	Black
Interface:	USB-C
Power Input:	100-240V~50/60Hz 600mA
Power Output:	5V=3A/9V=2.22A/12V=1.67A
Protocols:	PPS/PD3.0/QC4.0/AFC/FCP/BC1.2/Apple 2.4A
Total Output:	20W Max
Shell:	PC
Warranty:	1 Year
Packing:	Color Box



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance

FAQ

Q

Why does the battery charge get slower after 80%?

A

When the battery charge reaches 80%, it will start trickle mode intelligently, in order to better protect the battery from damage.

Q

Why is it normal for the cell phone to ring once and twice while charging?

A

According to the test of Vention Laboratory, it is normal to ring once or twice when charging. Please feel free to use it.

Q

Slight shaking when used with PD quick charging cable, is it normal?

A

Every product of Vention is produced in strict accordance with the standard, and passes strict quality testing before leaving the factory. Due to the small contact surface of USB C, slight shaking is a normal phenomenon, which does not affect the function of the product.

Package Display



Note: Packing difference exists for different meters or batches.
The photo is for reference only



1-port USB-C Wall Charger(20W)

Technical Features

Color	Black/White
Interface	USB-C
Shell	PC
Input	100-240V~50/60Hz, 600mA
Output	5V $\overline{=}$ 3A; 9V $\overline{=}$ 2.22A; 12V $\overline{=}$ 1.67A
Protocols	PPS/PD 3.0/QC 4.0/AFC/FCP/BC 1.2/Apple 2.4A

Color	Art.No.	EAN Code
White	FADW0-EU	6922794762626
Black	FADB0-EU	6922794762589



Package Contents

1-port USB-C Wall Charger(20W) x 1

Packaging Information

Packing Dimension	12*7*3cm
Packing Weight	0.081kg
Carton Dimension	48*29*31cm
Carton Qty	120pcs
Carton Weight	9.9kg

<https://ventiontech.com/>