

Ultra High Speed HDMI Cable 48 Gbps 8K 60 Hz silver 3 m certified

Description

This high-quality Ultra High Speed HDMI cable by Delock can be used to connect devices with an HDMI interface, such as televisions, Blu-ray players, monitors or projectors. By supporting a maximum bandwidth of 48 Gbps, content can be displayed in **8K Ultra HD** (7680 x 4320 @ 60 Hz) resolution.



Item no. 85368

EAN: 4043619853687

Country of origin: China

Package: Retail Box

Dynamic HDR and Dolby® Vision support

Supporting Dynamic HDR and Dolby® Vision, the cable is ideal for home cinema and gaming applications. Colours are realistically displayed with impressive depth, brightness and contrast are optimally reproduced.

Perfect sound with eARC support

The Delock HDMI cable supports **Enhanced ARC** (eARC). This allows HDMI devices such as Blu-ray players to be connected directly to the TV. The uncompressed audio signals are then transmitted directly and lossless to the connected sound system via the audio return channel.

Technical details

- Connectors:
 - 1 x HDMI male >
 - 1 x HDMI male
- Certified Ultra High Speed HDMI cable
- Cable gauge: 29 AWG
- Cable diameter: ca. 6.1 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 48 Gbps
- Resolution up to:
 - 7680 x 4320 @ 60 Hz
 - 5120 x 2880 @ 120 Hz
 - 3840 x 2160 @ 240 Hz
 - (depending on the system and the connected hardware)
- 3D support: up to 3840 x 2160 @ 120 Hz
 - (depending on the system and the connected hardware)
- Supports the 21:9 cinema aspect ratio
- Supports 1080p HFR (High Frame Rate) 3D
- Supports colour sampling in 4:4:4, 4:2:2 and 4:2:0 format
- Supports Display Stream Compression 1.2 (DSC)
- Supports Dolby® Vision
- Supports Dynamic HDR
- Supports HDCP 1.4 and 2.2
- Supports Game Mode VRR
- Supports eARC
- Up to 32 audio channels for speakers
- Up to 1536 kHz audio sampling rate
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Supports dynamic adjustment of lip synchronicity for audio / video delays
- Supports CEC 2.0 control commands
- Colour: silver
- Length incl. connectors: ca. 3 m

System requirements

- A free HDMI interface

Package content

- Ultra High Speed HDMI cable

Images



General

Specification:	Dolby® Vision HDCP 1.4 HDCP 2.2 HDMI 2.1 HDR10
Style:	both sides identical

Interface

Connector 1:	1 x HDMI-A male
Connector 2:	1 x HDMI-A male

Technical characteristics

Data transfer rate:	48 Gb/s
Maximum screen resolution:	7680 x 4320 @ 60 Hz

Physical characteristics

Connector finishing:	gold-plated
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	29 AWG
Shielding:	triple
Length:	3 m
Colour:	silver

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de