

Adapter-Plate

AP-R-160x160x16-50x50

Part no.:10.01.15.00296

<https://www.schmalz.com/10.01.15.00296>



Homepage > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Adapter-Plates AP-R > AP-R-160x160x16-50x50

Adapter-Plate AP for usage of Vacuum Blocks VCBL-B



for: Grid table systems

Working height H1 (max): 45 mm

Length L: 160 mm


Width B: 160 mm

Height H: 16 mm

grid: 50 x 50 mm

for slot: 5x5 / 7x7

Design Data



Attribute	Value
-----------	-------

B	160 mm
---	--------

H	16 mm
---	-------

L	160 mm
---	--------

Accessories

Adapter-Plate

AP-R-160x160x16-50x50

Part no.:10.01.15.00296

<https://www.schmalz.com/10.01.15.00296>



VCBL-B 140x130x29 TV

Part no.10.01.12.03165

Vacuum block

Dimensions (LxW): 140 x 130 mm

Height H: 29 mm

with: Sensing valve



VCBL-B 125x75x29 TV

Part no.10.01.12.03166

Vacuum block

Dimensions (LxW): 125 x 75 mm

Height H: 29 mm

with: Sensing valve



VCBL-B 120x50x29 TV

Part no.10.01.12.03167

Vacuum block

Dimensions (LxW): 120 x 50 mm

Height H: 29 mm

with: Sensing valve

Adapter-Plate

AP-R-160x160x16-50x50

Part no.:10.01.15.00296

<https://www.schmalz.com/10.01.15.00296>



VCBL-B 130x30x29 TV

Part no.10.01.12.03168

Vacuum block

Dimensions (LxW): 130 x 30 mm

Height H: 29 mm

with: Sensing valve



VCBL-B 140x130x48 TV

Part no.10.01.12.03169

Vacuum block

Dimensions (LxW): 140 x 130 mm

Height H: 48 mm

with: Sensing valve



VCBL-B 125x75x48 TV

Part no.10.01.12.03170

Vacuum block

Dimensions (LxW): 125 x 75 mm

Height H: 48 mm

with: Sensing valve

Adapter-Plate

AP-R-160x160x16-50x50

Part no.:10.01.15.00296

<https://www.schmalz.com/10.01.15.00296>



VCBL-B 120x50x48 TV

Part no.10.01.12.03171

Vacuum block

Dimensions (LxW): 120 x 50 mm

Height H: 48 mm

with: Sensing valve



VCBL-B 130x30x48 TV

Part no.10.01.12.03172

Vacuum block

Dimensions (LxW): 130 x 30 mm

Height H: 48 mm

with: Sensing valve



VCBL-B 140x130x74 TV

Part no.10.01.12.03173

Vacuum block

Dimensions (LxW): 140 x 130 mm

Height H: 74 mm

with: Sensing valve

Adapter-Plate

AP-R-160x160x16-50x50

Part no.:10.01.15.00296

<https://www.schmalz.com/10.01.15.00296>



VCBL-B 125x75x74 TV

Part no.10.01.12.03174

Vacuum block

Dimensions (LxW): 125 x 75 mm

Height H: 74 mm

with: Sensing valve



VCBL-B 120x50x74 TV

Part no.10.01.12.03175

Vacuum block

Dimensions (LxW): 120 x 50 mm

Height H: 74 mm

with: Sensing valve



VCBL-B 130x30x74 TV

Part no.10.01.12.03176

Vacuum block

Dimensions (LxW): 130 x 30 mm

Height H: 74 mm

with: Sensing valve