


O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



COM — NO

CIRCUIT: SPST
NORMALLY OPEN



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. RATING: 15A @125/250VAC
- ▲ 4. OPERATING FORCE: 50 $\pm$ 20 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
B	ECO-100836	REMOVE VDE RATING AND LOGO	04/18/22	JS						000021053
					TITLE					LS0851504F050C2C
					SCALE					3:2
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					DATE		DR		DWG	REV
					3/19/2009		BLR		Q950067	B