

NL-8022MP MD6 Serial PPS Multi GNSS Receiver u-blox 8 5 m

Description

The MD6 serial multi GNSS Receiver based on u-blox 8 chipset has a built-in antenna for high sensitivity. You can use this GNSS Receiver with a laptop and a suitable routing software for navigation. The MD6 universal connector enables the connection of optional USB or serial connecting cables. The NL-8022MP GNSS receiver is especially designed for installation on a white ground (boat, camper, bus etc.) It is unremarkable and fits into the vehicle concept due to its housing design.



Item no. 62529

EAN: 4043619625291

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connector: MD6 Navilock plug (RS-232) (USB or serial cable are optional available)
- Chipset: u-blox 8 UBX-M8030-KT
- Frequency:
 - GPS: L1, 1575.4200 MHz
 - GLONASS: L1, 1602 (k x 0,5625) MHz
 - BEIDOU COMPASS: B1, 1561.0980 MHz
 - GALILEO: E1, 1575.4200 MHz
 - QZSS: L1, 1575.4200 MHz
- Accepts the signals of up to 72 satellites at the same time
- Supports AssistNow online / offline, SBAS (WAAS, EGNOS, QZSS and MSAS)
- Supports NMEA 0183 protocols: GGA, GSA, GSV, RMC, VTG
- Auto Baud Rate up to 115200 bps
- PPS signal on pin 6 (LVTTTL 3.3 V)
- Update rate:
 - single GNSS: 18 Hz (e.g. GPS solo)
 - multi GNSS: 10 Hz (e.g. GPS+GLONASS)
- Sensibility max. -167 dBm
- IPX7 protection class
- Operating temperature: -20 °C ~ 60 °C
- Power supply: 5 V DC
- Current consumption: max. 45 mA
- Cold start in ca. 26 seconds

- Hot start in ca. 1 second
- Positioning accuracy: 2.5 m CEP (Circular Error Probable) and 2 m CEP with SBAS
- Cable length: ca. 5 m
- Dimensions (Ø x H without screw thread): ca. 62 mm x 21 mm

Microsoft Sensor and Location Platform ([Website](#))

- Profit from Windows applications (e.g. weather, maps, etc)
- Supporting the GNSS location platform API (32 bit)

System requirements

- Windows Vista/7/8/8.1/10, Linux Kernel 2.6, Mac OS X
- MD6 connection cable

Package content

- MD6 serial receiver
- Mounting material: stainless steel nut and washer
- Navilock support CD incl. driver and user manual

Images



General

Protection class:	IPX7
Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector:	1 x MD6 plug
------------	--------------

Technical characteristics

Operating voltage:	5 V DC
Chipset:	u-blox M8030-KT
Frequency range:	BEIDOU: B1, 1561.0980 MHz QZSS L1, 1575.4200 MHz GALILEO: E1 1575.4200 MHz GPS: L1, 1575.4200 MHz GLONASS: L1, 1602 (k x 0.5625) MHz
Operating temperature:	-20 °C ~ 60 °C
Current consumption:	45 mA
Sensitivity:	-167 dBm
Update rate:	up to 18 Hz

Physical characteristics

Housing colour:	white
Cable length incl. connectors:	5 m
Diameter:	62 mm
Length:	21 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@navilock.de
Website	www.navilock.de

