


ST - ICT test probe

mm [inch]




ST750 LA53 US

Minimum centers: 1.91 [.075]
Full travel: 6.35 [.250]
Working travel: 4.00 [.157]
Current rating: 3-4 A
Probe resistance: < 20mΩ
Operating temperature: -40°C up to +120°C
Plunger material: Steel / Gold plated
Barrel material: PhBr / Gold plated
Spring material: Stainless steel

Spring force at working stroke: 0.6 N [2.2 oz]

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Name		Date	Catalog Item:	
	Designed	M.K.	2024.05.17	ST750 LA53 US	
	Drawed			Drawing No.:	
	Checked				
Note					A4
			SHEET 1 OF 2		

ST - ICT test probe



Tools for the Test Probe

Tool Handle: TH1
Universal Insertion Bit: TBP7500
Insertion Bit: TBP7570

Tools for the Receptacle

Tool Handle Insertion: TH1
Tool Handle Insertion/Extraction: TH2
Universal Insertion Bit: TBP7500
Insertion Bit: TBR7535
Extraction Bit: TBR7570

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST750 LA53 US			
	Designed	M.K.	2024.05.17	Drawing No.:			
	Drawed						
	Checked						
Note					A4	SHEET 2 OF 2	EQUIPTEST TEST - SUPPORT - INNOVATE