

Antenna Cable N plug > N jack LMR195 RF195 6 m low loss

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 88683

EAN: 4043619886838

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x N plug >
 - 1 x N jack
- Impedance: 50 Ohm
- Cable type: LMR195, RF195
- Cable: coaxial
- Cable attenuation: 0.53 dB @ 2 GHz per meter
- Cable diameter: ca. 4.95 mm
- Cable colour: black
- Smallest bending radius: 12.7 mm
- Length incl. connectors (L): ca. 6 m


System requirements

- Device with two free N connectors

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x N male
Connector 2:	1 x N female

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial cable
Cable type:	RF195 LMR195
Cable attenuation:	0.53 dB @ 2.0 GHz per meter
Cable colour:	black
Cable length incl. connectors:	6 m
Smallest bending radius:	12.7 mm
Cable diameter:	4.95 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

