

SPECIFICATION

FOR

APPROVAL

Customer : _____

Description : Piezo Buzzer

Universal Model No. : UGPA30Y3309P

Universal Model No. : _____

Customer's Model No. : _____

ISSUE	CHECK	APPROVAL	CUSTOMER
ZhuYu 26.01.23	TangYuSheng 26.01.23	WangXueWen 26.01.23	



Universal (Changzhou) Electronics Co., Ltd.

Add: No. 16 Longhui Road, Wujin Hitech Development Zone,
Changzhou, Jiangsu, China

Tel: 86-519-88864155 88860185

E-mail: jim@China-buzzer.com

Fax: 86-519-88818807

<http://www.china-buzzer.com/>

SPECIFICATIONS

Model No.

UGPA30Y3309P

Page

1/5

1. ELECTRICAL AND ACOUSTICAL SPECIFICATION

	Item	Unit	Specifications
1-1	Rated Voltage (Square Wave)	Vp-p	9
1-2	Operating Voltage	Vp-p	5-90
1-3	* Rated Current (Max)	mA	10
1-4	* Min Sound Output at 3.3kHz/10cm	dB	90
1-5	* Resonant Frequency	Hz	3300
1-6	Capacitance at 120Hz	pF	25000±30%
1-7	Operating Temperature	℃	-30~+70
1-8	Storage Temperature	℃	-40~+85
1-9	Weight	g	2
1-10	Housing Material	NORYL(BLACK)	
1-11	Lead Pin Material	Red Copper (DSn)	
1-12	Tone Nature	Single	

* Value Applying at Rated Voltage (resonant frequency, 1/2 duty, square wave)

		26.01.23	ZhuYu	TangYuSheng	WangXueWen
Issue No	Description	Date	Issue	Check	Approval

Universal (Changzhou) Electronics Co., Ltd.

SPECIFICATIONS

Model No.

UGPA30Y3309P

Page

2/5

2.ENVIRONMENTAL TEST

	Item	Specifications
2-1	Storage in High temp.	Storage in $+70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
2-2	Storage in Low temp.	Storage in $-30^{\circ}\text{C} \pm 2^{\circ}\text{C}$ test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
2-3	Storage in Humidity	Storage in $+40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 90-95%RH test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
2-4	Thermal cycle test.	Make this test for 5 cycles without applying power, then expose to the room temperature for 2 hours.
2-5	Vibration test	Applying the vibration of amplitude 1.5mm and vibration frequency 10 to 55 Hz in each of 3 perpendicular directions for 2 hours.
2-6	Drop test	Free drop a unit from the height 70cm to the surface of 10mm thick board ,three directions(X,Y,Z).
2-7	Solderability test	Soldering temp.: $260 \pm 5^{\circ}\text{C}$ Heat applying time: $3 \pm 0.5\text{sec}$.

PASS CRITERION :

After these tests , the change of S.P.L shall be within $\pm 5 \text{ dB}$.

		26.01.23	ZhuYu	TangYuSheng	WangXueWen
Issue No	Description	Date	Issue	Check	Approval

Universal (Changzhou) Electronics Co., Ltd.

SPECIFICATIONS

Model No.

UGPA30Y3309P

Page

3/5

3.MEASURING METHOD(BUZZER MODE)

3-1 .Test Condition

3-1-1.STANDARD

Temperature : $25 \pm 3^{\circ}\text{C}$

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

3-1-2.JUDGEMENT

Temperature : $15 \sim 35^{\circ}\text{C}$


Relative humidity : 45% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

3-2 . Standard Test Fixture

3-2-1.rated Voltage(Square wave):9V

3-2-2.Resonant Frequency:3300Hz




		26.01.23	ZhuYu	TangYuSheng	WangXueWen
Issue No	Description	Date	Issue	Check	Approval

Universal (Changzhou) Electronics Co., Ltd.

SPECIFICATIONS	Model No.	UGPA30Y3309P
	Page	4/5

4.DIMENSIONS

Unless otherwise specified,tolerance: ± 0.5(unit:mm)



- 1、Housing meterial:NORYL (BLACK) wave solder and wash not allowed
- 2、This products working under 90Vp_p can not exceed 6 minutes

- 1) All parts must be meet to ROHS2.0.
- 2) Wave solder and wash not allowed.

4	PCB	1	Epoxy Board	
3	Housing	1	Black Noryl	
2	Pin	2	Red Copper	
1	Piezo element	1	Brass	
Part No.	Part Name	Q'TY	Material	Remark

		26.01.23	ZhuYu	TangYuSheng	WangXueWen
Issue No	Description	Date	Issue	Check	Approval

Universal (Changzhou) Electronics Co., Ltd.

SPECIFICATIONS


Model No.

UGPA30Y3309P


Page

5/5

5.PACKING



每盒放50只.
泡沫盒尺寸: 250*240*48mm



每箱放1000只.
纸箱尺寸: 500*260*490mm

		26.01.23	ZhuYu	TangYuSheng	WangXueWen
Issue No	Description	Date	Issue	Check	Approval

Universal (Changzhou) Electronics Co., Ltd.