

# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



CHARX connect comfort, AC charging cable, with infrastructure charging plug and free cable end, for charging electric vehicles (EV) with alternating current (AC), with protective cap, Type 2, IEC 62196-2, housing: black, gray, PHOENIX CONTACT logo, cable: 1.5 m, black, straight

## Product Description

AC charging cable with Infrastructure Plug and open cable end for charging electric vehicles (EV) with alternating current (AC), compatible with type 2 Infrastructure Socket Outlets at charging stations for E-Mobility (EVSE)

## Your advantages

- Complete product range
- Convenient handling due to the ergonomic, triple award-winning design
- Available with your logo on request – for consistent branding of your charging station
- Longitudinal water tightness reliably prevents water ingress
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Tested in accordance with automotive standards LV124, LV214, and LV215-2
- Tested in accordance with EV Ready 37 requirements
- Laser-marked mating face in accordance with DIN EN 17186

## Commercial Data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1628115       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales Key                            | XWBABC        |
| Product Key                          | XWBABC        |
| GTIN                                 | 4055626385327 |
| Weight per Piece (including packing) | 0.931 kg      |
| Weight per Piece (excluding packing) | 0.881 kg      |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

## Technical Data

### Product properties

|                   |                                                                                                                                                                             |
|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product type      | AC charging cable                                                                                                                                                           |
| Product family    | CHARX connect comfort                                                                                                                                                       |
| Application       | for charging electric vehicles (EV) with alternating current (AC)<br>compatible with type 2 infrastructure charging sockets at charging stations for electromobility (EVSE) |
| Type              | AC charging cable<br>with infrastructure charging plug and free cable end                                                                                                   |
| Design            | with protective cap                                                                                                                                                         |
| Locking type      | No locking option for U-lock                                                                                                                                                |
| Affixed logo      | PHOENIX CONTACT logo                                                                                                                                                        |
| Charging mode     | Mode 3                                                                                                                                                                      |
| Charging standard | Type 2                                                                                                                                                                      |

### Electrical properties

|                               |                                          |
|-------------------------------|------------------------------------------|
| Type of signal transmission   | Pulse width modulation                   |
| Note on the connection method | Crimp connection, cannot be disconnected |
| Coding                        | 220 $\Omega$ (between PE and PP)         |
| Type of charging current      | AC single-phase                          |
| Charging power                | 8 kW                                     |
| Charging current              | 32 A                                     |

### Power contact

|               |               |
|---------------|---------------|
| Number        | 3 (L1, N, PE) |
| Rated voltage | 250 V AC      |
| Rated current | 32 A          |

### Signal contact

|               |            |
|---------------|------------|
| Number        | 2 (CP, PP) |
| Rated voltage | 30 V AC    |
| Rated current | 2 A        |

### Dimensions

|        |          |
|--------|----------|
| Width  | 58 mm    |
| Height | 131.8 mm |
| Depth  | 233.4 mm |

### Material specifications

|                 |              |
|-----------------|--------------|
| Color (Housing) | black (9005) |
|                 | gray (7042)  |
|                 | black (9005) |
|                 | black (9005) |
|                 | black (9005) |

# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

|                                         |         |
|-----------------------------------------|---------|
| Material (Infrastructure charging plug) | Plastic |
|                                         | TPE-U   |
|                                         | Silver  |

## Cable/line

|                                |                                                                         |
|--------------------------------|-------------------------------------------------------------------------|
| Cable length                   | 1.5 m                                                                   |
| Wiring standards/regulations   | prEN 50620 / DIN EN 50620                                               |
| Wiring certifications          | VDE                                                                     |
| Cable weight                   | max. 305 kg/km                                                          |
| Cable type                     | Class 5                                                                 |
| Cable type                     | straight                                                                |
| Cable structure                | 3 x 6.0 mm <sup>2</sup> + 1 x 0.5 mm <sup>2</sup>                       |
| External cable diameter        | 12.8 mm ±0.4 mm                                                         |
| Outer sheath, material         | TPE-U                                                                   |
| Stripping length of the sheath | 70 mm ±5 mm                                                             |
| Cable resistance               | ≤ 0.0033 Ω/m (based on a power core, at an ambient temperature of 20°C) |
| Bending radius                 | min. 96 mm (7.5x diameter)                                              |

## Mechanical properties

### Mechanical data

|                             |         |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 10000 |
| Insertion force             | < 100 N |
| Withdrawal force            | < 100 N |

## Environmental and real-life conditions

### Ambient conditions

|                                                   |                                                                                                                                                                                                                |
|---------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Degree of protection Infrastructure charging plug | IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products) |
|                                                   | IP54                                                                                                                                                                                                           |
| Ambient temperature (operation)                   | -30 °C ... 50 °C                                                                                                                                                                                               |
| Ambient temperature (storage/transport)           | -40 °C ... 80 °C                                                                                                                                                                                               |
| Altitude                                          | 5000 m (above sea level)                                                                                                                                                                                       |

## Standards and regulations

### Standards

|                       |             |
|-----------------------|-------------|
| Standards/regulations | IEC 62196-2 |
|-----------------------|-------------|


# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable

1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>


## Drawings

Connection diagram



Pin assignment of Infrastructure Plug

Schematic diagram



Terminology definition


# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

Dimensional drawing




Infrastructure plug

# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable

1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

Schematic diagram



Operating instructions

# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

## Approvals

|  | IECEE CB Scheme        |                       |                   |                             |
|-----------------------------------------------------------------------------------|------------------------|-----------------------|-------------------|-----------------------------|
|                                                                                   | Approval ID: DE1-60744 |                       |                   |                             |
|                                                                                   | Nominal Voltage $U_N$  | Nominal Current $I_N$ | Cross Section AWG | Cross Section $\text{mm}^2$ |
|                                                                                   | 250 V                  | 32 A                  | -                 | -                           |

|  | VDE Zeichengenehmigung |                       |                   |                             |
|-----------------------------------------------------------------------------------|------------------------|-----------------------|-------------------|-----------------------------|
|                                                                                   | Approval ID: 40045392  |                       |                   |                             |
|                                                                                   | Nominal Voltage $U_N$  | Nominal Current $I_N$ | Cross Section AWG | Cross Section $\text{mm}^2$ |
|                                                                                   | 250 V                  | 32 A                  | -                 | -                           |

# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

## Classifications

### ECLASS

|               |          |
|---------------|----------|
| ECLASS-9.0    | 27144705 |
| ECLASS-10.0.1 | 27144705 |
| ECLASS-11.0   | 27144705 |

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC002897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|



# EV-T2G3P-1AC32A-1,5M6,0ESBK01 - AC charging cable



1628115

<https://www.phoenixcontact.com/pl/produkty/1628115>

## Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

|            |                                                                                                              |
|------------|--------------------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 10;                                                                    |
|            | For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads" |

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Sp. z o.o.

ul. Bierutowska 57-59, Budynek nr 3/A

51-317 Wrocław

71/ 39 80 410

[pxcpl@phoenixcontact.pl](mailto:pxcpl@phoenixcontact.pl)