






▲ CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. CONTACT RATING: 50mA @ 12VDC
4. CONTACT RESISTANCE: 100 mΩ MAX.
5. INSULATION RESISTANCE: 100MΩ MIN @ 500VDC.
- ▲ 6. OPERATING FORCE: 160 ± 50gf
7. TRAVEL: 0.2 ± 0.1mm
8. OPERATING TEMPERATURE: -25°C TO +70°C
9. OPERATING LIFE: 200,000 CYCLES
- ▲ 10. PART TO BE HALOGEN FREE MATERIALS
11. ▲ DENOTES CRITICAL PARAMETERS
12. 2011/65/EC (ROHS) COMPLIANT
13. PARTS TO BE PACKAGED IN TAPE & REEL, 450 PIECES PER REEL



▲ TAPE FOR
AUTOMATED PICKUP

CATHODE
SIDE

▲ COLOR MARK
ON CATHODE LEAD

▲ LED SPEC	UNITS	BLUE
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @ 20mA	V	3.2 TYP; 3.6 MAX
LUMINOUS INTENSITY @ 20mA	mcd	1100 TYP
WAVELENGTH	nm	465 - 475



E-SWITCH®

B	22576	ADD AUTOMATED PICKUP TAPE	11/3/16	MW
A	22557	New Release	10/21/16	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL3240F160BHF

SCALE 4:1	DATE 10/20/2016	DR rc	DWG N324014	REV B
--------------	--------------------	----------	----------------	----------