
TUNGSRAM™

Innovation is our heritage
EST. 1896




| 8 | A+ | 90 |
|---|---|---|
| kWh/1000h | energy class | lumens/watt |

# Tungsram LED A55

LED ECO A55 8W(55) 830 E27 TU

93093867

## Product information

A new shape designed to replace the A55 Halogen bulbs EEH 42W and 53W.

### Application areas

Hospitality

Home

# Tungsram LED A55

LED ECO A55 8W(55) 830 E27 TU

93093867

## Product data

| | |
|---|---|
| Product Code | 93093867 |
| Bulb Shape | A55 |
| Bulb Finish | white |
| Bulb maximum overall diameter [mm] | 57 |
| Nominal Length [mm] | 103 |
| Net weight per piece [g] | 48 |
| RoHS compliant | Yes |
| Brand | Tungsram |
| Cap/Base | E27 |

## Performance data

| | |
|---|---|
| Nominal/ Rated Beam Angle [°] | 180 |
| Rated Lumens [lm] | 720 |
| Weighted energy consumption [kWh/1000h] | 8.0 |
| Rated efficacy [lm/W] | 90 |
| Energy efficiency class (EEC) | A+ |
| Rated life L70/B50 [h] | 10000 |
| Nominal correlated colour temperature (CCT) [K]] | 3000 |
| Nominal lumens [lm] | 720 |
| Colour Rendering Index (CRI) [Ra] | 80 |

# Tungsram LED A55

LED ECO A55 8W(55) 830 E27 TU

93093867


## Electrical data


| | |
|---|---|
| Nominal lamp power factor... | >0.5 |
| Operating Temperature (MIN) [°C] | -20°C |
| Operating Temperature (MAX) [°C] | +40°C |
| Starting time (sec) | <0.5s |
| Warm up time up to 60% of full light output | Instant full light |
| Number of switching cycles | 50000 |
| Dimming Capability | No |
| Nominal lamp voltage range [V] | 220-240V 50/60Hz |
| Nominal power [W] | 8.0 |


## Logistic data

| | |
|---|---|
| DUN Code | 10064894502405 |
| EAN Code | 0064894502408 |
| Pack Quantity | 6 |
| Product status | Available |

## Photometric Data



# Tungsram LED A55

LED ECO A55 8W(55) 830 E27 TU

93093867

## Downloads & Links

Go to the catalog site (HTTP)

Photometry (IES)

Product datasheet (PDF)

Datasheet (PDF)

Images (HTTP)

Tungsram is a registered trademark of Tungsram Operations Kft.

tungsram.com

We in Tungsram Operations Kft. are constantly developing and improving our products. For this reason, all product descriptions in this catalogue are intended as a general guide, and we may change specifications from time to time in the interest of product development, without prior notification or public announcement. All descriptions in this publication present only general particulars of the goods to which they refer and shall not form part of any contract. Data in this guide has been obtained in controlled experimental conditions. However, Tungsram cannot accept any liability arising from the reliance on such data to the extent permitted by law.